



ZCK D15 →

Main

Range of product	OsiSense XC
Series name	Standard format
Product or component type	Limit switch head
Device short name	ZCKD
Head type	Rotary head
Product compatibility	XCKL XCKM
Associated body	ZCKL1H7 ZCKM1H29 ZCKL8 ZCKM9H29 ZCKM6H7 ZCKM5H29 ZCKL1 ZCKLD35H7 ZCKMD35 ZCKLD37 ZCKM8H29 ZCKMD37 ZCKM6H29 ZCKMD39 ZCKLD39H7 ZCKM1H7 ZCKLD39 ZCKM5H7 ZCKM7H7 ZCKM8 ZCKMD35H7 ZCKMD37H7 ZCKL5H7 ZCKMD31H7 ZCKMD31 ZCKM6 ZCKMD39H29 ZCKM7H29 ZCKL5 ZCKL6 ZCKM8H7 ZCKM5

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

ZCKLD31  
 ZCKMD31H29  
 ZCKL7H7  
 ZCKLD37H7  
 ZCKM7  
 ZCKLD35  
 ZCKL7  
 ZCKM9  
 ZCKM1  
 ZCKMD35H29  
 ZCKL6H7  
 ZCKMD37H29  
 ZCKL8H7  
 ZCKLD31H7  
 ZCKMD39H7

Movement of operating head	Rotary
Type of operator	Roller lever spring return thermoplastic
Type of approach	Lateral approach 2 directions

### Complementary

Switch actuation	By 30° cam
Positive opening	With
Head material	Metal

### Environment

Ambient air temperature for operation	-25...70 °C
Ambient air temperature for storage	-40...70 °C
Environmental characteristic	Standard environment

### Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 0951 - Schneider Electric declaration of conformity <a href="#">Schneider Electric declaration of conformity</a>
REACH	Reference not containing SVHC above the threshold <a href="#">Reference not containing SVHC above the threshold</a>
Product end of life instructions	Need no specific recycling operations

### Contractual warranty

Warranty period	18 months
-----------------	-----------