

ZCKD54

limit switch head ZCKD - steel square rod lever 3 mm L = 125 mm



Main

Range of product	OsiSense XC
Series name	Standard format
Product or component type	Limit switch head
Device short name	ZCKD
Head type	Rotary head
Product compatibility	XCKS
Associated body	ZCKS1H29 ZCKS5H29 ZCKS1 ZCKS6H29 ZCKS6 ZCKS9H29 ZCKS9 ZCKSD31 ZCKSD39 ZCKSD31H29 ZCKSD37H29 ZCKS8H29 ZCKSD35 ZCKS7 ZCKS2H29 ZCKSD39H29 ZCKS8 ZCKS2 ZCKS7H29 ZCKS5 ZCKSD35H29 ZCKSD37
Movement of operating head	Rotary
Type of operator	Rod lever spring return metal (square rod 3 mm, L = 125 mm)
Type of approach	Lateral approach 2 directions

Complementary

Switch actuation	By any moving part
Positive opening	Without
Head material	Plastic

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications.

Environment

Ambient air temperature for operation	-25...70 °C
Ambient air temperature for storage	-40...70 °C
Environmental characteristic	Standard environment

Offer Sustainability

RoHS (date code: YYWW)	Will not be compliant Will not be compliant
REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold
Product end of life instructions	Need no specific recycling operations

Contractual warranty

Warranty period	18 months
-----------------	-----------