

ZCKE655

limit switch head ZCKE - side steel roller plunger
vertical - +120 °C



Main

Range of product	OsiSense XC
Series name	Standard format
Product or component type	Limit switch head
Device short name	ZCKE
Head type	Plunger head
Product compatibility	XCKJ
Associated body	ZCKJ11H7 ZCKJ8 ZCKJ9 ZCKJ1 ZCKJ5H7 ZCKJD35H29 ZCKJ6H29 ZCKJ2H29 ZCKJ8H29 ZCKJD39H7 ZCKJ8H7 ZCKJ2H7 ZCKJD31H29 ZCKJ6 ZCKJ21 ZCKJ5 ZCKJ6H7 ZCKJD31 ZCKJ1H29 ZCKJ7H7 ZCKJ11 ZCKJ11H29 ZCKJ7 ZCKJ9H29 ZCKJ5H29 ZCKJD39H29 ZCKJ7H29 ZCKJD37H7 ZCKJD37 ZCKJD35H7 ZCKJ1H7

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

ZCKJ21H7
ZCKJ9H7
ZCKJD31H7
ZCKJ2
ZCKJD35
ZCKJD39
ZCKJ21H29
ZCKJD37H29

Movement of operating head	Linear
Type of operator	Side roller plunger spring return metal (with vertical roller)
Type of approach	Vertical approach 2 directions

Complementary

Switch actuation	By 30° cam
Positive opening	With
Product weight	0.205 kg
Head material	Metal

Environment

Ambient air temperature for operation	10...120 °C
Ambient air temperature for storage	10...120 °C
Environmental characteristic	High temperature

Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 1440 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold
Product end of life instructions	Need no specific recycling operations

Contractual warranty

Warranty period	18 months
-----------------	-----------