

NetShelter Platform Quick SX/SV Comparisons

Feature	NetShelter SV	NetShelter SX	Notes
Compatibility			
InfraStruxure		<input checked="" type="checkbox"/>	SV – not optimized for row based infrastructure
Small IT Solution	<input checked="" type="checkbox"/>	<input checked="" type="checkbox"/>	
Convenience			
Primarily toolless rack components		<input checked="" type="checkbox"/>	SV – Mounting rails, accessory brackets are non-toolless. full height side panels. Roof not removable.
Agility			
Adjustable mounting rails	<input checked="" type="checkbox"/>	<input checked="" type="checkbox"/>	SV – fasteners not captive, alignment feature different
Accessory mounting channel	<input checked="" type="checkbox"/>	<input checked="" type="checkbox"/>	SV – 4 brackets, install full-height accessories with no adjustment

Feature	NetShelter SV	NetShelter SX	Notes
Casters	<input checked="" type="checkbox"/>	<input checked="" type="checkbox"/>	SX – low profile, SV – normal profile
Roof eyebolt support		<input checked="" type="checkbox"/>	
Safety			
Shock packaging options for equipment shipment		<input checked="" type="checkbox"/>	SV – no packaging options and not designed for equipment shipment
Seismic rated		<input checked="" type="checkbox"/>	SX – capable of IBC Zone 4 Seismic
Load rating	Static: 2205 lb (1000 kg) Dynamic: 1014 lb (460 kg)	Static: 3000 lb (1363 kg) Dynamic: 2250 lb (1022 kg)	
UL Approved	<input checked="" type="checkbox"/>	<input checked="" type="checkbox"/>	
Heights	42, 48U	24, 42, 45, 48U	
Widths	600, 800mm	600, 750mm (700 Japan Only)	

Feature	NetShelter SX	NetShelter SV
Depths	825, 1070, 1200mm	1060, 1200mm (1000mm China only)
InfraStruxure Designer Integration	Yes	No (SISD only)
Roof	Toolless removal, brushes	Fixed and structural, multiple cable entry openings
Eyebolt support	Yes	No
Front /Rear door	69% perforation pattern	69% perforation pattern
Side panel	Split half-height	Single full height
Rear cable management	Multiple channels, full height	4 accessory brackets
Caster	Low-profile	Normal-profile
Joining bracket	600mm & 24-in preinstalled	600mm preinstalled, 24-in hardware bag
Cable brushes in roof	Yes	800mm only

Feature	NetShelter SX	NetShelter SV
Vertical mounting rail adjustability	Easy full adjustability	Multiple adjustment points
Shock packaging options	Yes	No
Seismic capabilities	Yes	No
UL Approved	Yes	Yes