Product data sheet

Specifications

Mureva FIX - installation tie - 194x9 mm - 100 pieces

ENN47942

Main

Product Range	Mureva FIX
Product Type	Installation tie
Colour Tint	Black
Quantity Per Set	100 pieces

Complementary

Minimum Tightening Diameter	10 mm
Maximum Tightening Diameter	42 mm
Resistance To Tearing	Resistance to tearing: 36 daN Ø 20 mm
Material	PA (polyamide) 12 Rislan®
Length	194 mm
Width	9 mm
Net Weight	0.003 kg

Environment

Maximum Humidity Absorption	0.9 %
Operating Temperature	-60…85 °C 100 °C during 1000 hours 120 °C maximum
Flame Retardance	HB conforming to UL 94
Standards	EN 50146
Environmental Characteristic	UV resistant

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	8.5 cm
Package 1 Width	10.5 cm
Package 1 Length	20.5 cm
Package 1 Weight	3.0 g
Unit Type Of Package 2	BB1
Number Of Units In Package 2	100
Package 2 Height	8.5 cm

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Package 2 Width	10.5 cm
Package 2 Length	20.5 cm
Package 2 Weight	1.3 kg
Unit Type Of Package 3	CAR
Number Of Units In Package 3	2000
Package 3 Height	33.0 cm
Package 3 Width	35.0 cm
Package 3 Length	39.5 cm
Package 3 Weight	6.28 kg

Contractual warranty

Warranty	18 months

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO_2 products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >

Transparency

RoHS/REACh

Well-being performance

Reach Free Of Svhc	
Toxic Heavy Metal Free	
Mercury Free	
Rohs Exemption Information	Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations