

Product data sheet

Specifications



15M SIDE PANEL PRISMA G IP30

01043

⚠ Discontinued on: Apr 25, 2023

⚠ Discontinued

Main

Range	Prisma
Range Of Product	Prisma G
Product Or Component Type	Side panel
Accessory / Separate Part Category	Spare part Enclosure accessory
Range Compatibility	Prisma Prisma G enclosure
Installation Description	Wall-mounted enclosure
Mounting Location	Side
Number Of Vertical Modules [50 Mm]	15

Complementary

Protective Treatment	Electrophoresis treatment and hot-polymerised polyester epoxy powder
Surface Finish	Glossy Textured epoxy polyester
Colour	White (RAL 9001)
Special Colour Options	Yes
Width	200 mm
Height	775 mm
Depth	180 mm
Net Weight	1.58 kg
Quantity Per Set	Set of 1

Environment

Ip Degree Of Protection	IP30
Ik Degree Of Protection	IK07 IK08

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	5.0 cm
Package 1 Width	20.5 cm

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Package 1 Length	113.5 cm
Package 1 Weight	1.812 kg
Unit Type Of Package 2	P12
Number Of Units In Package 2	45
Package 2 Height	80.0 cm
Package 2 Width	80.0 cm
Package 2 Length	120.0 cm
Package 2 Weight	95.0 kg

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency RoHS/REACH

Well-being performance

✓ Reach Free Of Svhc

✓ Toxic Heavy Metal Free

✓ Mercury Free

✓ Rohs Exemption Information Yes

✓ Halogen Free Plastic Parts Product

Certifications & Standards

Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
-------------------	---

China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
-----------------------	---

Environmental Disclosure	Product Environmental Profile
--------------------------	---

Circularity Profile	End of Life Information
---------------------	---