# Product data sheet

Specifications

## panel GLASS TOUCH PANELS for hotels - modbus - 10 buttons - sample order

LSSMBU10NS

## Main

| | |
|---|---|
| **Product Name** | Glass Touch Panels |
| **Product Type** | Configurable touchscreen panel |
| **Device Application** | Bell switch<br>Hotel<br>Energy efficiency<br>Monitoring<br>Lighting<br>Ventilation<br>Remote control |
| **Color Buttons Display Options** | Champagne gold<br>White<br>Silver<br>Black |
| **Colour Tint** | Panel: black<br>Panel: white<br>Panel: silver<br>Panel: champagne gold<br>Button: white<br>Button: amber<br>Button: blue<br>Button: light green<br>Button: red<br>Button: grey |
| **Module Configuration** | Configurated with the Glass Touch Panel Design tool |

## Complementary

| | |
|---|---|
| **Control Button Type** | 10 configurable touch button |
| **Local Signalling** | configurable |
| **[Us] Rated Supply Voltage** | 24 V DC |
| **Current Consumption** | 30 mA |
| **Communication Port Protocol** | Modbus serial with RS485 port(s) |
| **Mounting Mode** | Magnetic<br>Snap-in |
| **Height** | 160 mm (standard)<br>160 mm (optional) |
| **Width** | 105 mm (standard)<br>95 mm (optional) |
| **Depth** | 33 mm (standard)<br>33 mm (optional) |
| **Relative Humidity** | 10…95 %, non-condensing (operation) |
| **Order Type** | Mockup sample order |

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

## Environment

| | |
|---|---|
| **Ambient Air Temperature For Storage** | 0…60 °C |
| **Ambient Air Temperature For Operation** | 0…45 °C |

## Packing Units

| | |
|---|---|
| **Unit Type Of Package 1** | PCE |
| **Number Of Units In Package 1** | 1 |
| **Package 1 Height** | 5.5 cm |
| **Package 1 Width** | 13.5 cm |
| **Package 1 Length** | 27.0 cm |
| **Package 1 Weight** | 600.0 g |
| **Unit Type Of Package 2** | S03 |
| **Number Of Units In Package 2** | 10 |
| **Package 2 Height** | 30.0 cm |
| **Package 2 Width** | 30.0 cm |
| **Package 2 Length** | 40.0 cm |
| **Package 2 Weight** | 7.0 kg |
| **Unit Type Of Package 3** | P12 |
| **Number Of Units In Package 3** | 240 |
| **Package 3 Height** | 105.0 cm |
| **Package 3 Width** | 80.0 cm |
| **Package 3 Length** | 120.0 cm |
| **Package 3 Weight** | 183.0 kg |