

# Product data sheet

Specifications



## IP30 REINFORCED PLAIN DOOR IK10 W650

01224

⚠ Discontinued on: Jan 31, 2024

⚠ To be end-of-service on: Apr 30, 2025

⚠ Discontinued - Service only

### Main

Range	Prisma
Range Of Product	Prisma P
Product Or Component Type	Door
Range Compatibility	Prisma Prisma P cubicle
Provided Equipment	door handle keylock (key 405) hinge other keylock and insert to be ordered separately
Enclosure Mounting	Floor-standing
Type Of Door	Plain
Ip Degree Of Protection	IP30

### Complementary

Installation Description	Cubicle - width 650 mm
Door Opening Side	Reversible
Number Of Locks	3
Door Opening Angle	120 °
Number Of Vertical Modules [50 Mm]	36
Enclosure Material	Treated sheet steel
Quantity Per Set	Set of 1
Height	2000 mm
Width	650 mm
Net Weight	24.6 kg
Surface Finish	Matt Smooth
Colour	White (RAL 9001)

### Environment

Ik Degree Of Protection	IK10 conforming to EN/IEC 62262
Standards	IEC 61439-1 IEC 61439-2
Protective Treatment	Electrophoresis treatment and hot-polymerised polyester epoxy powder

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

# Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	8.000 cm
Package 1 Width	69.500 cm
Package 1 Length	203.500 cm
Package 1 Weight	23.350 kg
Unit Type Of Package 2	PAL
Number Of Units In Package 2	10
Package 2 Height	95.000 cm
Package 2 Width	200.000 cm
Package 2 Length	120.000 cm
Package 2 Weight	246.000 kg

## Sustainability

**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency   RoHS/REACH

## Well-being performance

✓ Reach Free Of Svhc

✓ Toxic Heavy Metal Free

✓ Mercury Free

✓ Rohs Exemption Information   Yes

## Certifications & Standards

**Eu Rohs Directive**   Pro-active compliance (Product out of EU RoHS legal scope)  
[EU RoHS Declaration](#)

**China Rohs Regulation**   [China RoHS declaration](#)  
Pro-active China RoHS declaration (out of China RoHS legal scope)

**Environmental Disclosure**   [Product Environmental Profile](#)

**Circularity Profile**   [End of Life Information](#)