

Product data sheet

Specifications

W850 ADJUSTABLE MODULAR DEVICE RAIL PRISMA G



03007

⚠ Discontinued on: Apr 25, 2023

⚠ Discontinued

Main

Range	Prisma
Range Of Product	Prisma G
Product Or Component Type	Rail
Accessory / Separate Part Category	Installation accessory
Range Compatibility	Prisma Prisma G
Type Of Rail	Modular Adjustable
Installed Device	ComPact: fixed NG160 without earth leakage protection ComPact: fixed NG160 with earth leakage protection ComPact: fixed NSXm without earth leakage protection - control: toggle - vertical installation ComPact: fixed NSXm with earth leakage protection - control: toggle - vertical installation
Poles Description	7 x 3P: fixed NG160 5 x 4P: fixed NG160 3 x 3P: fixed NG160 2 x 4P: fixed NG160 1 x 3P or 4P: fixed NSXm vertical installation

Complementary

Installation Description	Floor-standing enclosure - width 850 mm
Number Of Vertical Modules [50 Mm]	5 module(s): NG160 without earth leakage protection , direct in 850 mm Widefloor-standing enclosure 5 module(s): NSXm without earth leakage protection , direct in 850 mm Widefloor-standing enclosure 5 module(s): NG160 with earth leakage protection , direct in 850 mm Widefloor-standing enclosure 5 module(s): NSXm with earth leakage protection , direct in 850 mm Widefloor-standing enclosure
9 Mm Pitches	72
Quantity Per Set	Set of 1
Height	82 mm
Width	662 mm
Depth	169 mm
Net Weight	0.4 kg
Colour	Natural
Material	Metal
Thickness	1.5 mm

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Environment

Standards	IEC 61439-2
	IEC 61439-1

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	5.6 cm
Package 1 Width	10.5 cm
Package 1 Length	69.4 cm
Package 1 Weight	400.0 g
Unit Type Of Package 2	BB1
Number Of Units In Package 2	10
Package 2 Height	15.5 cm
Package 2 Width	33.0 cm
Package 2 Length	73.5 cm
Package 2 Weight	4.6 kg
Unit Type Of Package 3	P12
Number Of Units In Package 3	140
Package 3 Height	75.0 cm
Package 3 Width	80.0 cm
Package 3 Length	120.0 cm
Package 3 Weight	65.24 kg

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency RoHS/REACH

Well-being performance

✓ Reach Free Of Svhc

✓ Toxic Heavy Metal Free

✓ Mercury Free

✓ Rohs Exemption Information Yes

✓ Halogen Free Plastic Parts Product

Certifications & Standards

Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
-------------------	---

China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
-----------------------	---

Environmental Disclosure	Product Environmental Profile
--------------------------	---