


# Product data sheet

Specifications



## MOUNTING PLATE ISFT 160 FIXED VERTICAL W300

03123

 **Discontinued on:** Apr 25, 2023

 **Discontinued**

### Main

Range	Prisma
Range Of Product	Prisma G
Product Or Component Type	Mounting plate
Accessory / Separate Part Category	Installation accessory
Range Compatibility	Prisma Prisma Pack 250 duct Prisma Prisma G duct
Installation Description	Floor-standing duct - width 300 mm Wall-mounted duct - width 300 mm Pack enclosure - width 300 mm
Installed Device	FuPact: fixed ISFT160 - control: fuse carriers handle - vertical installation
Poles Description	1 x 3P: fixed ISFT160 vertical installation
Number Of Vertical Modules [50 Mm]	6 module(s): ISFT160, direct in 300 mm Widefloor-standing duct 6 module(s): ISFT160, direct in 300 mm Widewall-mounted duct 9 module(s): ISFT160, direct in 300 mm WidePack enclosure
Standards	IEC 61439-2
Product Certifications	ASEFA

### Complementary

Protective Treatment	Electrophoresis treatment and hot-polymerised polyester epoxy powder
Surface Finish	Smooth Matt
Colour	White (RAL 9001)
Width	300 mm
Height	150 mm
Net Weight	0.4 kg
Functional Unit	300 mm Prisma G floor-standing duct FuPact ISFT160 fixed fuse carriers handle vertical 3P 1 direct 6 150 mm 300 mm Prisma G wall-mounted duct FuPact ISFT160 fixed fuse carriers handle vertical 3P 1 direct 6 150 mm 300 mm Prisma Pack 250 Pack enclosure FuPact ISFT160 fixed fuse carriers handle vertical 3P 1 direct 9 150 mm

### Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	6.500 cm

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Package 1 Width	10.000 cm
Package 1 Length	22.000 cm
Package 1 Weight	400.000 g
Unit Type Of Package 2	CAR
Number Of Units In Package 2	12
Package 2 Height	20.000 cm
Package 2 Width	40.000 cm
Package 2 Length	60.000 cm
Package 2 Weight	5.560 kg
Unit Type Of Package 3	P12
Number Of Units In Package 3	48
Package 3 Height	55.000 cm
Package 3 Width	80.000 cm
Package 3 Length	120.000 cm
Package 3 Weight	22.240 kg

## Sustainability

**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency   RoHS/REACH

## Well-being performance

✓ Reach Free Of Svhc

✓ Toxic Heavy Metal Free

✓ Mercury Free

✓ Rohs Exemption Information   [Yes](#)

✓ Halogen Free Plastic Parts Product

## Certifications & Standards

Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
-------------------	---

China Rohs Regulation	<a href="#">China RoHS declaration</a> Pro-active China RoHS declaration (out of China RoHS legal scope)
-----------------------	---

Environmental Disclosure	<a href="#">Product Environmental Profile</a>
--------------------------	---