

Product data sheet

Specifications



M+FR PLATE INS/INV250 H.FIX.TOG. W600 6M PACK250

03264

⚠ Discontinued on: Apr 25, 2023

⚠ Discontinued

Main

Range	Prisma
Range Of Product	Prisma G
Product Or Component Type	Incoming functional unit
Accessory / Separate Part Category	Installation accessory
Range Compatibility	Prisma Prisma Pack 250 enclosure
Type Of Front Plate	Cut-out
Installed Device	ComPact: fixed INS250 - control: direct front rotary handle - horizontal installation ComPact: fixed INV250 - control: direct front rotary handle - vertical installation
Poles Description	1 x 3P: mounting plate support: INS250 horizontal installation 1 x 4P: mounting plate support: INS250 horizontal installation 1 x 4P: mounting plate support: INV250 vertical installation 1 x 3P: mounting plate support: INV250 vertical installation
Operating Position	Vertical

Complementary

Enclosure/Cubicle Description	Pack enclosure - width 600 mm
Number Of Vertical Modules [50 Mm]	6
Standards	IEC 61439-2 IEC 61439-1
Product Certifications	ASEFA
Surface Finish	Smooth Matt
Protective Treatment	Electrophoresis treatment and hot-polymerised polyester epoxy powder
Colour	White (RAL 9001)
Height	300 mm
Width	600 mm
Net Weight	2.85 kg
Quantity Per Set	Set of 1
Functional Unit	600 mm Prisma Pack 250 Pack enclosure ComPact INS250 fixed direct front rotary handle horizontal 3P 1 connection block 6 87.5 mm 600 mm Prisma Pack 250 Pack enclosure ComPact INS250 fixed direct front rotary handle horizontal 4P 1 connection block 6 87.5 mm 600 mm Prisma Pack 250 Pack enclosure ComPact INV250 fixed direct front rotary handle vertical 3P 1 direct 6 87.5 mm 600 mm Prisma Pack 250 Pack enclosure ComPact INV250 fixed direct front rotary handle vertical 4P 1 direct 6 87.5 mm

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Environment

Ip Degree Of Protection	IP30
-------------------------	------

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	5.500 cm
Package 1 Width	51.500 cm
Package 1 Length	68.000 cm
Package 1 Weight	2.850 kg
Unit Type Of Package 2	P12
Number Of Units In Package 2	20
Package 2 Height	67.000 cm
Package 2 Width	80.000 cm
Package 2 Length	120.000 cm
Package 2 Weight	57.000 kg

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency RoHS/REACH

Well-being performance

✓ Reach Free Of Svhc

✓ Toxic Heavy Metal Free

✓ Mercury Free

✓ Rohs Exemption Information [Yes](#)

✓ Halogen Free Plastic Parts Product

Certifications & Standards

Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
-------------------	---

China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
-----------------------	---

Environmental Disclosure	Product Environmental Profile
--------------------------	---