


Product data sheet

Specifications



FRONT PLATE INF32/40 3P VERTICAL WIDTH 600/650 3M

03312

⚠ Discontinued on: Feb 28, 2021

⚠ Discontinued

Main

Range	Prisma
Range Of Product	Prisma G Prisma P
Product Or Component Type	Front plate
Accessory / Separate Part Category	Installation accessory
Range Compatibility	Prisma Prisma G enclosure Prisma Prisma P cubicle
Type Of Front Plate	Cut-out
Installed Device	FuPact: fixed INF32 - control: extended rotary handle - vertical installation FuPact: fixed INF40 - control: extended rotary handle - vertical installation
Poles Description	4 x 3P: mounting plate support: INF32 vertical installation 4 x 3P: mounting plate support: INF40 vertical installation
Operating Position	Vertical

Complementary

Enclosure/Cubicle Description	Floor-standing enclosure - width 600 mm Wall-mounted enclosure - width 600 mm Cubicle - width 650 mm depth 400 mm
Number Of Vertical Modules [50 Mm]	3
Standards	IEC 61439-1 IEC 61439-2
Product Certifications	ASEFA
Material	Steel
Surface Finish	Matt Smooth
Protective Treatment	Electrophoresis treatment and hot-polymerised polyester epoxy powder
Colour	White (RAL 9001)
Height	150 mm
Width	500 mm
Net Weight	0.66 kg
Quantity Per Set	Set of 1

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Functional Unit	600 mm Prisma G floor-standing enclosure FuPact INF32 fixed extended rotary handle vertical 3P 4 direct 3 600 mm Prisma G wall-mounted enclosure FuPact INF32 fixed extended rotary handle vertical 3P 4 direct 3 600 mm Prisma G floor-standing enclosure FuPact INF40 fixed extended rotary handle vertical 3P 4 direct 3 600 mm Prisma G wall-mounted enclosure FuPact INF40 fixed extended rotary handle vertical 3P 4 direct 3 650 mm 400 mm Prisma P cubicle FuPact INF32 fixed extended rotary handle vertical 3P 4 direct 3 650 mm 400 mm Prisma P cubicle FuPact INF40 fixed extended rotary handle vertical 3P 4 direct 3
-----------------	--

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	3 cm
Package 1 Width	16 cm
Package 1 Length	51 cm
Package 1 Weight	660 g

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency RoHS/REACH

Well-being performance

✓ Reach Free Of Svhc

✓ Toxic Heavy Metal Free

✓ Mercury Free

✓ Rohs Exemption Information Yes

✓ Halogen Free Plastic Parts Product

Certifications & Standards

Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
-------------------	---

China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
-----------------------	---

Environmental Disclosure	Product Environmental Profile
--------------------------	---