


Product data sheet

Specifications



FRONT PLATE ISFT250 HORIZONTAL W600 5M

03328

⚠ Discontinued on: Apr 25, 2023

⚠ Discontinued

Main

Range	Prisma
Range Of Product	Prisma G
Product Or Component Type	Front plate
Accessory / Separate Part Category	Installation accessory
Range Compatibility	Prisma Prisma G enclosure Prisma Prisma Pack 250 enclosure
Type Of Front Plate	Cut-out
Installed Device	FuPact: fixed ISFT250 - control: fuse carriers handle - horizontal installation
Poles Description	1 x 3P: mounting plate support: ISFT250 horizontal installation
Operating Position	Horizontal

Complementary

Enclosure/Cubicle Description	Floor-standing enclosure - width 600 mm Wall-mounted enclosure - width 600 mm Pack enclosure - width 600 mm
Connection Position	Direct connection
Number Of Vertical Modules [50 Mm]	5
Standards	IEC 61439-2 IEC 61439-1
Product Certifications	ASEFA
Material	Steel
Surface Finish	Smooth Matt
Protective Treatment	Electrophoresis treatment and hot-polymerised polyester epoxy powder
Colour	White (RAL 9001)
Height	250 mm
Width	500 mm
Net Weight	0.78 kg
Quantity Per Set	Set of 1
Functional Unit	600 mm Prisma G floor-standing enclosure FuPact ISFT250 fixed fuse carriers handle horizontal 3P 1 direct 6 600 mm Prisma G wall-mounted enclosure FuPact ISFT250 fixed fuse carriers handle horizontal 3P 1 direct 6 600 mm Prisma Pack 250 Pack enclosure FuPact ISFT250 fixed fuse carriers handle horizontal 3P 1 direct 6

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	3.0 cm
Package 1 Width	25.0 cm
Package 1 Length	50.0 cm
Package 1 Weight	780.0 g
Unit Type Of Package 2	CAR
Number Of Units In Package 2	10
Package 2 Height	17.0 cm
Package 2 Width	27.0 cm
Package 2 Length	53.0 cm
Package 2 Weight	8.16 kg
Unit Type Of Package 3	P12
Number Of Units In Package 3	90
Package 3 Height	32.0 cm
Package 3 Width	80.0 cm
Package 3 Length	120.0 cm
Package 3 Weight	85.44 kg

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency RoHS/REACH

Well-being performance

✓ Reach Free Of Svhc

✓ Toxic Heavy Metal Free

✓ Mercury Free

✓ Rohs Exemption Information [Yes](#)

✓ Halogen Free Plastic Parts Product

Certifications & Standards

Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
-------------------	---

China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
-----------------------	---

Environmental Disclosure	Product Environmental Profile
--------------------------	---