


# Product data sheet

Specifications



## M.PL.3 4 V.WITHD.NS250 POLYP.

03423

⚠ Discontinued on: Apr 25, 2023

⚠ Discontinued

### Main

Range	Prisma
Range Of Product	Prisma P
Product Or Component Type	Mounting plate
Accessory / Separate Part Category	Installation accessory
Range Compatibility	Prisma Prisma P cubicle
Installation Description	Cubicle - width 650 mm depth 400 mm
Installed Device	ComPact: plug-in NSX100...160 without earth leakage protection - control: toggle - vertical installation ComPact: plug-in NSX250 without earth leakage protection - control: toggle - vertical installation ComPact: plug-in NSX100...160 with earth leakage protection - control: toggle - vertical installation ComPact: plug-in NSX250 with earth leakage protection - control: toggle - vertical installation
Poles Description	4 x 3P: plug-in NSX100...160 vertical installation 3 x 4P: plug-in NSX100...160 vertical installation 4 x 3P: plug-in NSX250 vertical installation 3 x 4P: plug-in NSX250 vertical installation
Number Of Vertical Modules [50 Mm]	7 module(s): NSX100...160 without earth leakage protection , Linergy FC in 650 mm Widecubicle 8 module(s): NSX250 without earth leakage protection , Linergy FC in 650 mm Widecubicle 9 module(s): NSX100...160 with earth leakage protection , Linergy FC in 650 mm Widecubicle 10 module(s): NSX250 with earth leakage protection , Linergy FC in 650 mm Widecubicle
Standards	IEC 61439-2
Product Certifications	ASEFA

### Complementary

Protective Treatment	Electrophoresis treatment and hot-polymerised polyester epoxy powder
Surface Finish	Matt Smooth
Colour	White (RAL 9001)
Width	603 mm
Height	202 mm
Depth	372 mm
Net Weight	2.98 kg

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Functional Unit	650 mm 400 mm Prisma P cubicle ComPact NSX100...160 without plug-in toggle vertical 3P 4 Linergy FC 7 87.5 mm 650 mm 400 mm Prisma P cubicle ComPact NSX100...160 without plug-in toggle vertical 4P 3 Linergy FC 7 87.5 mm 650 mm 400 mm Prisma P cubicle ComPact NSX250 without plug-in toggle vertical 3P 4 Linergy FC 8 62.5 mm 650 mm 400 mm Prisma P cubicle ComPact NSX250 without plug-in toggle vertical 4P 3 Linergy FC 8 62.5 mm 650 mm 400 mm Prisma P cubicle ComPact NSX100...160 with plug-in toggle vertical 3P 4 Linergy FC 9 87.5 mm 650 mm 400 mm Prisma P cubicle ComPact NSX100...160 with plug-in toggle vertical 4P 3 Linergy FC 9 87.5 mm 650 mm 400 mm Prisma P cubicle ComPact NSX250 with plug-in toggle vertical 3P 4 Linergy FC 10 87.5 mm 650 mm 400 mm Prisma P cubicle ComPact NSX250 with plug-in toggle vertical 4P 3 Linergy FC 10 87.5 mm
-----------------	--

## Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	2.500 cm
Package 1 Width	20.300 cm
Package 1 Length	58.000 cm
Package 1 Weight	3.050 kg
Unit Type Of Package 2	S04
Number Of Units In Package 2	6
Package 2 Height	30.000 cm
Package 2 Width	40.000 cm
Package 2 Length	60.000 cm
Package 2 Weight	19.300 kg
Unit Type Of Package 3	P12
Number Of Units In Package 3	72
Package 3 Height	105.000 cm
Package 3 Width	80.000 cm
Package 3 Length	120.000 cm
Package 3 Weight	222.240 kg

## Sustainability

**Green Premium™** label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency   RoHS/REACH

## Well-being performance



Mercury Free



RoHS Exemption Information

[Yes](#)



Halogen Free Plastic Parts Product

## Certifications & Standards

**Eu RoHS Directive**

Pro-active compliance (Product out of EU RoHS legal scope)

[EU RoHS Declaration](#)

**China RoHS Regulation**

[China RoHS declaration](#)

Product out of China RoHS scope. Substance declaration for your information

**Environmental Disclosure**

[Product Environmental Profile](#)

**Circularity Profile**

[End of Life Information](#)