


# Product data sheet

Specifications



## MOUNTING PLATE SOURCE CHANGEOVER NSX/INS/INV 250 3P/4P ROTARY VERTICAL

03428

⚠ Discontinued on: Apr 25, 2023

⚠ Discontinued

### Main

Range	Prisma
Range Of Product	Prisma P
Product Or Component Type	Mounting plate
Accessory / Separate Part Category	Installation accessory
Range Compatibility	Prisma Prisma P cubicle
Installation Description	Cubicle - width 650 mm depth 400 mm
Installed Device	ComPact: fixed INS250 source changeover - control: direct front rotary handle - vertical installation ComPact: fixed INS250 source changeover - control: mechanical interlock - vertical installation ComPact: fixed INV250 source changeover - control: mechanical interlock - vertical installation Source changeover: fixed NSX100...250 source changeover - control: mechanical interlock - vertical installation
Poles Description	2 x 3P: fixed INS250 source changeover vertical installation 2 x 4P: fixed INS250 source changeover vertical installation 2 x 3P: fixed INV250 source changeover vertical installation 2 x 4P: fixed INV250 source changeover vertical installation 2 x 3P: fixed NSX100...250 source changeover vertical installation 2 x 4P: fixed NSX100...250 source changeover vertical installation
Number Of Vertical Modules [50 Mm]	9 module(s): INS250 source changeover, direct in 650 mm Widecubicle 9 module(s): INV250 source changeover, direct in 650 mm Widecubicle 10 module(s): NSX100...250 source changeover, direct in 650 mm Widecubicle
Standards	IEC 61439-2
Product Certifications	ASEFA

### Complementary

Protective Treatment	Electrophoresis treatment and hot-polymerised polyester epoxy powder
Surface Finish	Matt Smooth
Colour	White (RAL 9001)
Width	536 mm
Height	289 mm
Net Weight	3.3 kg

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Functional Unit	650 mm 400 mm Prisma P cubicle ComPact INS250 source changeover fixed direct front rotary handle vertical 3P 2 direct 9 112.5 mm 650 mm 400 mm Prisma P cubicle ComPact INS250 source changeover fixed direct front rotary handle vertical 4P 2 direct 9 112.5 mm 650 mm 400 mm Prisma P cubicle ComPact INS250 source changeover fixed mechanical interlock vertical 3P 2 direct 9 112.5 mm 650 mm 400 mm Prisma P cubicle ComPact INS250 source changeover fixed mechanical interlock vertical 4P 2 direct 9 112.5 mm 650 mm 400 mm Prisma P cubicle ComPact INV250 source changeover fixed mechanical interlock vertical 3P 2 direct 9 112.5 mm 650 mm 400 mm Prisma P cubicle ComPact INV250 source changeover fixed mechanical interlock vertical 4P 2 direct 9 112.5 mm 650 mm 400 mm Prisma P cubicle source changeover NSX100...250 source changeover fixed mechanical interlock vertical 3P 2 direct 10 112.5 mm 650 mm 400 mm Prisma P cubicle source changeover NSX100...250 source changeover fixed mechanical interlock vertical 4P 2 direct 10 112.5 mm
-----------------	--

## Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	3.500 cm
Package 1 Width	29.000 cm
Package 1 Length	57.500 cm
Package 1 Weight	3.300 kg
Unit Type Of Package 2	CAR
Number Of Units In Package 2	4
Package 2 Height	20.000 cm
Package 2 Width	40.000 cm
Package 2 Length	60.000 cm
Package 2 Weight	13.920 kg
Unit Type Of Package 3	P12
Number Of Units In Package 3	32
Package 3 Height	75.000 cm
Package 3 Width	80.000 cm
Package 3 Length	120.000 cm
Package 3 Weight	111.360 kg

## Sustainability

**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency   RoHS/REACH

## Well-being performance

✓ Reach Free Of Svhc

✓ Toxic Heavy Metal Free

✓ Mercury Free

✓ Rohs Exemption Information   Yes

✓ Halogen Free Plastic Parts Product

## Certifications & Standards

Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
-------------------	---

China Rohs Regulation	<a href="#">China RoHS declaration</a> Pro-active China RoHS declaration (out of China RoHS legal scope)
-----------------------	---

Environmental Disclosure	<a href="#">Product Environmental Profile</a>
--------------------------	---

Circularity Profile	<a href="#">End of Life Information</a>
---------------------	---