


Product data sheet

Specifications

Mounting Plate Vert. Fixed MTZ1/ NT 3P/4P 1600A W650 Prisma P



03484

⚠ Discontinued on: Jan 11, 2022

⚠ Discontinued

Main

Range	Prisma
Range Of Product	Prisma P
Product Or Component Type	Mounting plate
Accessory / Separate Part Category	Installation accessory
Range Compatibility	Prisma Prisma P cubicle
Installation Description	Cubicle - width 650 mm depth 400 mm Cubicle - width 650 mm depth 800 mm
Installed Device	Masterpact: fixed NT06...10 - control: toggle - vertical installation Masterpact: fixed NT06...10 - control: motor mechanism - vertical installation Masterpact: fixed NT12 - control: toggle - vertical installation Masterpact: fixed NT12 - control: motor mechanism - vertical installation Masterpact: fixed NT16 - control: toggle - vertical installation Masterpact: fixed NT16 - control: motor mechanism - vertical installation
Poles Description	1 x 3P: fixed NT06...10 vertical installation 1 x 4P: fixed NT06...10 vertical installation 1 x 3P: fixed NT12 vertical installation 1 x 4P: fixed NT12 vertical installation 1 x 3P: fixed NT16 vertical installation 1 x 4P: fixed NT16 vertical installation
Number Of Vertical Modules [50 Mm]	11 module(s): NT06...10, rear connection on adaptor in 650 mm Widecubicle 16 module(s): NT06...10, rear connection on Canalis in 650 mm Widecubicle 11 module(s): NT12, rear connection on adaptor in 650 mm Widecubicle 16 module(s): NT12, rear connection on Canalis in 650 mm Widecubicle 11 module(s): NT16, rear connection on adaptor in 650 mm Widecubicle 16 module(s): NT16, rear connection on Canalis in 650 mm Widecubicle 12 module(s): NT06...10, front connection on adaptor in 650 mm Widecubicle 17 module(s): NT06...10, front connection on Canalis in 650 mm Widecubicle 14 module(s): NT12, front connection on adaptor in 650 mm Widecubicle 17 module(s): NT12, front connection on Canalis in 650 mm Widecubicle 14 module(s): NT16, front connection on adaptor in 650 mm Widecubicle
Standards	IEC 61439-2
Product Certifications	ASEFA

Complementary

Protective Treatment	Electrophoresis treatment and hot-polymerised polyester epoxy powder
Surface Finish	Smooth Matt
Colour	White (RAL 9001)
Width	650 mm
Height	30 mm
Net Weight	2.4 kg

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

650 mm 800 mm Prisma P cubicle Masterpact NT16 fixed toggle vertical 4P 1 rear
connection on adaptor 11 337.5 mm
650 mm 800 mm Prisma P cubicle Masterpact NT16 fixed motor mechanism vertical
4P 1 rear connection on adaptor 11 337.5 mm
650 mm 800 mm Prisma P cubicle Masterpact NT16 fixed toggle vertical 4P 1 rear
connection on Canalis 16 687.5 mm
650 mm 800 mm Prisma P cubicle Masterpact NT16 fixed motor mechanism vertical
4P 1 rear connection on Canalis 16 687.5 mm

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	3 cm
Package 1 Width	13.5 cm
Package 1 Length	57 cm
Package 1 Weight	2.3 kg

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency RoHS/REACH

Well-being performance



Mercury Free



RoHS Exemption Information

[Yes](#)



Halogen Free Plastic Parts Product

Certifications & Standards

Eu RoHS Directive

Pro-active compliance (Product out of EU RoHS legal scope)

[EU RoHS Declaration](#)

China RoHS Regulation

[China RoHS declaration](#)

Product out of China RoHS scope. Substance declaration for your information

Environmental Disclosure

[Product Environmental Profile](#)

Circularity Profile

[End of Life Information](#)