


Product data sheet

Specifications



FRONT PLATE WITH 3 CUT-OUT 96x96METERING DEV/P-BUTTON WIDTH 600/650 3M

03911

 **Discontinued on:** Apr 25, 2023

 **Discontinued**

Main

Range	Prisma
Range Of Product	Prisma G Prisma P
Product Or Component Type	Front plate
Accessory / Separate Part Category	Installation accessory
Range Compatibility	Prisma Prisma G enclosure Prisma Prisma P cubicle
Type Of Front Plate	Cut-out
Type Of Front Plate	Cut-out
Installed Device	Vigilohm: IM20 Vigilohm: IM20H Human-switchboard interface: 96 x 96 mm device Human-switchboard interface: HSI PowerLogic: PM400...800 Vigilohm: IM10 Vigilohm: IM10H Enerlin'X: FDM121

Complementary

Enclosure/Cubicle Description	Floor-standing enclosure - width 600 mm Wall-mounted enclosure - width 600 mm Cubicle - width 650 mm depth 400 mm
Number Of Vertical Modules [50 Mm]	3
Standards	IEC 61439-2 IEC 61439-1
Product Certifications	ASEFA
Material	Steel
Surface Finish	Matt Smooth
Protective Treatment	Electrophoresis treatment and hot-polymerised polyester epoxy powder
Colour	White (RAL 9001)
Height	150 mm
Width	500 mm
Net Weight	0.46 kg
Quantity Per Set	Set of 1

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Functional Unit	600 mm Prisma G floor-standing enclosure human-switchboard interface 96 x 96 mm device 3 3
	600 mm Prisma G wall-mounted enclosure human-switchboard interface 96 x 96 mm device 3 3
	650 mm 400 mm Prisma P cubicle human-switchboard interface 96 x 96 mm device 3 3
	600 mm Prisma G floor-standing enclosure human-switchboard interface HSI 3 3
	600 mm Prisma G wall-mounted enclosure human-switchboard interface HSI 3 3
	650 mm 400 mm Prisma P cubicle human-switchboard interface HSI 3 3
	600 mm Prisma G floor-standing enclosure PowerLogic 3 3
	600 mm Prisma G wall-mounted enclosure PowerLogic 3 3
	650 mm 400 mm Prisma P cubicle PowerLogic 3 3
	650 mm 400 mm Prisma P cubicle Vigilohm 3 3
	600 mm Prisma G floor-standing enclosure Enerlin'X FDM121 3 3
	600 mm Prisma G wall-mounted enclosure Enerlin'X FDM121 3 3
	650 mm 400 mm Prisma P cubicle Enerlin'X FDM121 3 3

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	3.0 cm
Package 1 Width	16.0 cm
Package 1 Length	51.0 cm
Package 1 Weight	500.0 g
Unit Type Of Package 2	CAR
Number Of Units In Package 2	10
Package 2 Height	17.5 cm
Package 2 Width	17.0 cm
Package 2 Length	53.0 cm
Package 2 Weight	5.25 kg
Unit Type Of Package 3	P12
Number Of Units In Package 3	90
Package 3 Height	32.0 cm
Package 3 Width	80.0 cm
Package 3 Length	120.0 cm
Package 3 Weight	45.52 kg

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency RoHS/REACH

Well-being performance

✓ Reach Free Of Svhc

✓ Toxic Heavy Metal Free

✓ Mercury Free

✓ Rohs Exemption Information [Yes](#)

✓ Halogen Free Plastic Parts Product

Certifications & Standards

Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
-------------------	---

China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
-----------------------	---

Environmental Disclosure	Product Environmental Profile
--------------------------	---