

# Product data sheet

Specifications



## FRONT PLATE WITH 1 PRE CUT-OUT 96x96 W300 3M

03923

 **Discontinued on:** Apr 25, 2023

 **Discontinued**

### Main

Range	Prisma
Range Of Product	Prisma G Prisma P
Product Or Component Type	Front plate
Accessory / Separate Part Category	Installation accessory
Range Compatibility	Prisma Prisma G duct Prisma Prisma P cubicle
Type Of Front Plate	Cut-out
Type Of Front Plate	Cut-out
Installed Device	Human-switchboard interface: 96 x 96 mm device Human-switchboard interface: HSI PowerLogic: PM400...800 Enerlin'X: FDM121

### Complementary

Enclosure/Cubicle Description	Floor-standing duct - width 300 mm Wall-mounted duct - width 300 mm Cubicle duct - width 400 mm depth 400 mm
Number Of Vertical Modules [50 Mm]	3
Standards	IEC 61439-1 IEC 61439-2
Product Certifications	ASEFA
Surface Finish	Matt Smooth
Protective Treatment	Electrophoresis treatment and hot-polymerised polyester epoxy powder
Colour	White (RAL 9001)
Height	150 mm
Net Weight	0.62 kg
Quantity Per Set	Set of 1

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Functional Unit	400 mm 400 mm Prisma P cubicle human-switchboard interface 96 x 96 mm device 1 3
	400 mm 400 mm Prisma P cubicle human-switchboard interface HSI 1 3
	400 mm 400 mm Prisma P cubicle PowerLogic 1 3
	300 mm Prisma G floor-standing duct human-switchboard interface 96 x 96 mm device 1 3
	300 mm Prisma G wall-mounted duct human-switchboard interface 96 x 96 mm device 1 3
	300 mm Prisma G floor-standing duct human-switchboard interface HSI 1 3
	300 mm Prisma G wall-mounted duct human-switchboard interface HSI 1 3
	300 mm Prisma G floor-standing duct PowerLogic 1 3
	300 mm Prisma G wall-mounted duct PowerLogic 1 3
	400 mm 400 mm Prisma P cubicle Enerlin'X FDM121 1 3
	300 mm Prisma G floor-standing duct Enerlin'X FDM121 1 3
	300 mm Prisma G wall-mounted duct Enerlin'X FDM121 1 3

## Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	0.2 cm
Package 1 Width	15.0 cm
Package 1 Length	25.0 cm
Package 1 Weight	330.0 g
Unit Type Of Package 2	CAR
Number Of Units In Package 2	12
Package 2 Height	17.0 cm
Package 2 Width	20.0 cm
Package 2 Length	28.5 cm
Package 2 Weight	4.0 kg
Unit Type Of Package 3	P12
Number Of Units In Package 3	192
Package 3 Height	35.0 cm
Package 3 Width	80.0 cm
Package 3 Length	120.0 cm
Package 3 Weight	78.0 kg

## Sustainability

**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency   RoHS/REACH

## Well-being performance

✓ Reach Free Of Svhc

✓ Toxic Heavy Metal Free

✓ Mercury Free

✓ Rohs Exemption Information   [Yes](#)

✓ Halogen Free Plastic Parts Product

## Certifications & Standards

Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
-------------------	---

China Rohs Regulation	<a href="#">China RoHS declaration</a> Pro-active China RoHS declaration (out of China RoHS legal scope)
-----------------------	---

Environmental Disclosure	<a href="#">Product Environmental Profile</a>
--------------------------	---