

Product data sheet

Specifications



DOOR FOR CAPACITORS W650

03970

⚠ Discontinued on: Apr 25, 2023

⚠ Discontinued

Main

Range	Prisma
Range Of Product	Prisma P
Product Or Component Type	Door
Range Compatibility	Prisma Prisma P cubicle
Provided Equipment	door handle keylock (key 405) hinge other keylock and insert to be ordered separately
Enclosure Mounting	Floor-standing
Type Of Door	Cut-out
Ip Degree Of Protection	IP30

Complementary

Installation Description	Cubicle - width 650 mm
Door Opening Side	Left
Number Of Locks	2
Door Opening Angle	120 °
Number Of Vertical Modules [50 Mm]	36
Enclosure Material	Treated sheet steel
Quantity Per Set	Set of 1
Height	2000 mm
Width	650 mm
Depth	35 mm
Net Weight	17.36 kg
Surface Finish	Smooth Matt
Colour	White (RAL 9001)

Environment

Ik Degree Of Protection	IK08 conforming to EN/IEC 62262
Standards	IEC 61439-1 IEC 61439-2

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Protective Treatment	Electrophoresis treatment and hot-polymerised polyester epoxy powder
----------------------	--

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	5.500 cm
Package 1 Width	68.000 cm
Package 1 Length	203.500 cm
Package 1 Weight	17.650 kg
Unit Type Of Package 2	PAL
Number Of Units In Package 2	10
Package 2 Height	95.000 cm
Package 2 Width	202.000 cm
Package 2 Length	120.000 cm
Package 2 Weight	197.500 kg

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency RoHS/REACH

Well-being performance



Mercury Free



RoHS Exemption Information

Yes

Certifications & Standards

Eu RoHS Directive

Pro-active compliance (Product out of EU RoHS legal scope)

[EU RoHS Declaration](#)

China RoHS Regulation

[China RoHS declaration](#)

Product out of China RoHS scope. Substance declaration for your information

Environmental Disclosure

[Product Environmental Profile](#)

Circularity Profile

[End of Life Information](#)