


# Product data sheet

Specifications



## VERTICAL PARTITION H36M PRISMA G IP30

04335

⚠ Discontinued on: Apr 25, 2023

⚠ Discontinued

### Main

Range	Prisma
Range Of Product	Prisma G
Product Or Component Type	Partition
Accessory / Separate Part Category	Insulation accessory
Range Compatibility	Prisma Prisma G enclosure
Ip Degree Of Protection	IP30
Product Specific Application	To partition vertical lateral busbars

### Complementary

Installation Direction	Vertical
Quantity Per Set	Set of 1
Height	1830 mm
Surface Finish	Matt Smooth
Protective Treatment	Electrophoresis treatment and hot-polymerised polyester epoxy powder

### Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	2.500 cm
Package 1 Width	12.500 cm
Package 1 Length	80.500 cm
Package 1 Weight	2.360 kg
Unit Type Of Package 2	BB1
Number Of Units In Package 2	10
Package 2 Height	15.500 cm
Package 2 Width	22.500 cm
Package 2 Length	82.000 cm
Package 2 Weight	23.600 kg
Unit Type Of Package 3	P06
Number Of Units In Package 3	30

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Package 3 Height	77.000 cm
Package 3 Width	80.000 cm
Package 3 Length	60.000 cm
Package 3 Weight	73.000 kg

## Sustainability

**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency   RoHS/REACH

## Well-being performance

✓ Reach Free Of Svhc

✓ Toxic Heavy Metal Free

✓ Mercury Free

✓ Rohs Exemption Information   Yes

✓ Halogen Free Plastic Parts Product

## Certifications & Standards

Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
-------------------	---

China Rohs Regulation	<a href="#">China RoHS declaration</a> Pro-active China RoHS declaration (out of China RoHS legal scope)
-----------------------	---

Environmental Disclosure	<a href="#">Product Environmental Profile</a>
--------------------------	---