


# Product data sheet

Specifications



## DRILLED VERTICAL FLAT BAR LINERGY BS 60X5 L1675

04516

 **Discontinued on:** Apr 25, 2023

 **Discontinued**

### Main

Range	Linergy
Range Of Product	Linergy
Product Or Component Type	Copper busbar
Product Name	Linergy BS
Range Compatibility	Prisma Prisma P enclosure
Busbar Description	Flat bar
Quantity Per Set	Set of 1

### Complementary

Installation Direction	Vertical, operating position: rear Vertical, operating position: lateral
Installation Description	Cubicle - width 650 mm Cubicle - width 650 + 150 mm
[Ie] Rated Operational Current	800 A at 35 °C
[Icw] Rated Short-Time Withstand Current	15 kA (1 s) for 3 supports (lateral position) 30 kA (1 s) for 5 supports (lateral position) 40 kA (1 s) for 7 supports (lateral position) 15 kA (1 s) for 3 supports (rear position) 30 kA (1 s) for 5 supports (rear position) 40 kA (1 s) for 7 supports (rear position)
Permissible Current	800 A at 35 °C: <= IP31 750 A at 35 °C: > IP31
Busbar Cross Section	60 x 5 mm
Length	1675 mm
Net Weight	4.54 kg
Type Of Busbar Connection	Ø 10 mm drilled hole
Connection Pitch	Connection each 25 mm
Support Thickness	5 mm

### Environment

Standards	IEC 61439-1 IEC 61439-2
Product Certifications	ASEFA

### Packing Units

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	1.5 cm
Package 1 Width	14.0 cm
Package 1 Length	183.0 cm
Package 1 Weight	4.54 kg
Unit Type Of Package 2	P2M
Number Of Units In Package 2	80
Package 2 Height	39.0 cm
Package 2 Width	200.0 cm
Package 2 Length	120.0 cm
Package 2 Weight	363.2 kg

## Sustainability

**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency   RoHS/REACH

## Well-being performance

✓ Reach Free Of Svhc

✓ Toxic Heavy Metal Free

✓ Mercury Free

✓ Rohs Exemption Information   [Yes](#)

✓ Pvc Free

✓ Halogen Free Plastic Parts Product

## Certifications & Standards

Eu Rohs Directive	Compliant <a href="#">EU RoHS Declaration</a>
China Rohs Regulation	<a href="#">China RoHS declaration</a> Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	<a href="#">End of Life Information</a>