

# Product data sheet

Specifications



## EXTENSION ENCLOSURE 2 ROWS PRISMA PACK 160

08012

 **Discontinued on:** Apr 25, 2023

 **Discontinued**

### Main

Range	Prisma
Range Of Product	Prisma G
Product Or Component Type	Enclosure extension
Enclosure Type	Empty enclosure
Enclosure/Cubicle Description	Wall-mounted enclosure - width 555 mm
Enclosure Mounting	Flush with kit Surface
Type Of Front Plate	Without to be ordered separately
Number Of Vertical Modules [50 Mm]	6
Number Of Horizontal Rows	2
Number Of 18 Mm Modules Per Row	24
Standards	IEC 61439-1 IEC 62208 IEC 61439-2 IEC 61439-3

### Complementary

[Ui] Rated Insulation Voltage	750 V
[In] Rated Current	160 A at 40 °C conforming to IEC 61439-2
Electrical Insulation Class	Class I
Protective Treatment	Electrophoresis treatment and hot-polymerised polyester epoxy powder
Surface Finish	Matt Smooth
Colour	White (RAL 9001)
Width	555 mm
Height	480 mm
Depth	157 mm
Net Weight	7.22 kg
Quantity Per Set	Set of 1

### Environment

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Ip Degree Of Protection	IP30 with door
	IP31 with door and canopy
	IP43 with door, canopy and IP43 gasket
	IP30 without door
Ik Degree Of Protection	IK07 without door conforming to EN/IEC 62262
	IK08 with door

## Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	16.0 cm
Package 1 Width	50.0 cm
Package 1 Length	57.0 cm
Package 1 Weight	7.23 kg
Unit Type Of Package 2	P12
Number Of Units In Package 2	10
Package 2 Height	95.0 cm
Package 2 Width	80.0 cm
Package 2 Length	120.0 cm
Package 2 Weight	84.3 kg

## Sustainability

**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency   RoHS/REACH

## Well-being performance

✓ Reach Free Of Svhc

✓ Toxic Heavy Metal Free

✓ Mercury Free

✓ Rohs Exemption Information   [Yes](#)

## Certifications & Standards

**Eu Rohs Directive**   Pro-active compliance (Product out of EU RoHS legal scope)  
[EU RoHS Declaration](#)

**China Rohs Regulation**   [China RoHS declaration](#)  
Pro-active China RoHS declaration (out of China RoHS legal scope)

**Environmental Disclosure**   [Product Environmental Profile](#)