

Product data sheet

Specifications



PLAIN DOOR W600 9M PRISMA G IP30

08123

⚠ Discontinued on: Apr 25, 2023

⚠ Discontinued

Main

Range	Prisma
Range Of Product	Prisma G
Product Or Component Type	Door
Range Compatibility	Prisma Prisma G enclosure
Provided Equipment	door handle keylock (key 405) other keylock and insert to be ordered separately 2 hinge
Type Of Door	Plain
Ip Degree Of Protection	IP43 with door, canopy and IP43 gasket IP30 without door IP40 with door IP41 with door and canopy

Complementary

Installation Description	Wall-mounted enclosure - width 600 mm Extension enclosure - width 600 mm
Door Opening Side	Reversible
Number Of Locks	1
Door Opening Angle	130 °
Number Of Vertical Modules [50 Mm]	9
Enclosure Material	Handle: polyamide Cover frame: treated sheet steel
Quantity Per Set	Set of 1
Height	480 mm
Width	600 mm
Depth	36 mm
Net Weight	3.38 kg
Surface Finish	Matt Smooth
Colour	White (RAL 9001)

Environment

Ik Degree Of Protection	IK08 conforming to EN/IEC 62262
-------------------------	---------------------------------

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Standards	IEC 61439-1
	IEC 61439-2
Protective Treatment	Electrophoresis treatment and hot-polymerised polyester epoxy powder

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	5.5 cm
Package 1 Width	51.5 cm
Package 1 Length	64.0 cm
Package 1 Weight	4.06 kg
Unit Type Of Package 2	P12
Number Of Units In Package 2	30
Package 2 Height	97.5 cm
Package 2 Width	80.0 cm
Package 2 Length	120.0 cm
Package 2 Weight	133.8 kg

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency RoHS/REACH

Well-being performance



Mercury Free



RoHS Exemption Information

Yes

Certifications & Standards

Eu RoHS Directive

Pro-active compliance (Product out of EU RoHS legal scope)

[EU RoHS Declaration](#)

China RoHS Regulation

[China RoHS declaration](#)

Product out of China RoHS scope. Substance declaration for your information

Environmental Disclosure

[Product Environmental Profile](#)