

Product data sheet

Specifications



PLAIN DUCT DOOR W300 9M PRISMA G IP30

08183

⚠ Discontinued on: Apr 25, 2023

⚠ Discontinued

Main

| | |
|---------------------------|--|
| Range | Prisma |
| Range Of Product | Prisma G |
| Product Or Component Type | Door |
| Range Compatibility | Prisma Prisma G duct |
| Provided Equipment | door handle keylock (key 405) other keylock and insert to be ordered separately 2 hinge |
| Type Of Door | Plain |
| Ip Degree Of Protection | IP43 with door, canopy and IP43 gasket IP30 without door IP40 with door IP41 with door and canopy |

Complementary

| | |
|------------------------------------|---|
| Installation Description | Wall-mounted duct - width 300 mm |
| Door Opening Side | Reversible |
| Number Of Locks | 1 |
| Door Opening Angle | 130 ° |
| Number Of Vertical Modules [50 Mm] | 9 |
| Enclosure Material | Handle: polyamide Cover frame: treated sheet steel |
| Quantity Per Set | Set of 1 |
| Height | 480 mm |
| Width | 300 mm |
| Depth | 33 mm |
| Net Weight | 2.08 kg |
| Surface Finish | Matt Smooth |
| Colour | White (RAL 9001) |

Environment

| | |
|-------------------------|---------------------------------|
| Ik Degree Of Protection | IK08 conforming to EN/IEC 62262 |
|-------------------------|---------------------------------|

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

| | |
|----------------------|--|
| Standards | IEC 61439-2 |
| | IEC 61439-1 |
| Protective Treatment | Electrophoresis treatment and hot-polymerised polyester epoxy powder |

Packing Units

| | |
|------------------------------|-----------|
| Unit Type Of Package 1 | PCE |
| Number Of Units In Package 1 | 1 |
| Package 1 Height | 5.0 cm |
| Package 1 Width | 33.5 cm |
| Package 1 Length | 52.5 cm |
| Package 1 Weight | 2.524 kg |
| Unit Type Of Package 2 | P12 |
| Number Of Units In Package 2 | 60 |
| Package 2 Height | 93.0 cm |
| Package 2 Width | 80.0 cm |
| Package 2 Length | 120.0 cm |
| Package 2 Weight | 162.12 kg |

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency RoHS/REACH

Well-being performance

✓ Mercury Free

✓ Rohs Exemption Information [Yes](#)

Certifications & Standards

| | |
|--------------------------|---|
| Eu Rohs Directive | Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration |
| China Rohs Regulation | China RoHS declaration Product out of China RoHS scope. Substance declaration for your information |
| Environmental Disclosure | Product Environmental Profile |