


# Product data sheet

Specifications



## DUCT (REAR ENCLOSURE+PLAIN DOOR) W300 15M PRISMA G IP55

08344

⚠ Discontinued on: Apr 25, 2023

⚠ Discontinued

### Main

Range	Prisma
Range Of Product	Prisma G
Product Or Component Type	Rear panel Door
Device Application	Low voltage electrical distribution
Enclosure Type	Functional enclosure delivered in kit form
Enclosure Mounting	Surface
Provided Equipment	1 x door for enclosure
Additional Information	Can be combined side by side and one on top of another
Type Of Front Plate	Without
Number Of Vertical Modules [50 Mm]	15
Number Of 18 Mm Modules Per Row	10
Standards	IEC 62208 IEC 61439-2 IEC 61439-1

### Complementary

[Ui] Rated Insulation Voltage	1000 V
[In] Rated Current	630 A at 40 °C conforming to IEC 61439-2
Electrical Insulation Class	Class I
Protective Treatment	Electrophoresis treatment and hot-polymerised polyester epoxy powder
Surface Finish	Smooth Matt
Colour	White (RAL 9001)
Width	300 mm
Height	850 mm
Depth	260 mm
Net Weight	15.04 kg
Quantity Per Set	Set of 1

### Environment

Ip Degree Of Protection	IP55 with door
-------------------------	----------------

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Ik Degree Of Protection	IK10 with door conforming to EN/IEC 62262
Mechanical Robustness	Seismic tests - 2.5G conforming to IEC 60068-2-57

## Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	11.000 cm
Package 1 Width	37.000 cm
Package 1 Length	84.000 cm
Package 1 Weight	14.571 kg
Unit Type Of Package 2	P12
Number Of Units In Package 2	4
Package 2 Height	37.000 cm
Package 2 Width	80.000 cm
Package 2 Length	120.000 cm
Package 2 Weight	60.160 kg

## Sustainability

**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency   RoHS/REACH

## Well-being performance

✓ Reach Free Of Svhc

✓ Toxic Heavy Metal Free

✓ Mercury Free

✓ Rohs Exemption Information   Yes

## Certifications & Standards

**Eu Rohs Directive**   Pro-active compliance (Product out of EU RoHS legal scope)  
[EU RoHS Declaration](#)

**China Rohs Regulation**   [China RoHS declaration](#)  
Pro-active China RoHS declaration (out of China RoHS legal scope)

**Environmental Disclosure**   [Product Environmental Profile](#)