


Product data sheet

Specifications

IP30 2-PART GL.PL.W400 D400



08494

⚠ Discontinued on: Apr 25, 2023

⚠ Discontinued

Main

Range Of Product	Prisma P
Range	Prisma
Range Compatibility	Prisma Prisma P cubicle duct
Product Or Component Type	Gland plate
Product Compatibility	IP31 enclosure

Complementary

Enclosure/Cubicle Description	Cubicle duct - width 400 mm
Type Of Gland Plate	Two part gland plate
Material	Treated sheet steel
Quantity Per Set	Set of 1
Width	400 mm
Depth	400 mm
Net Weight	2.04 kg
Surface Finish	Matt Smooth
Protective Treatment	Electrophoresis treatment and hot-polymerised polyester epoxy powder
Colour	White (RAL 9001)

Environment

Ip Degree Of Protection	IP31
-------------------------	------

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	4.500 cm
Package 1 Width	14.300 cm
Package 1 Length	36.900 cm
Package 1 Weight	1.996 kg
Unit Type Of Package 2	S02
Number Of Units In Package 2	5

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Package 2 Height	15.000 cm
Package 2 Width	30.000 cm
Package 2 Length	40.000 cm
Package 2 Weight	10.230 kg

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency RoHS/REACH

Well-being performance

✓ Reach Free Of Svhc

✓ Toxic Heavy Metal Free

✓ Mercury Free

✓ Rohs Exemption Information [Yes](#)

✓ Halogen Free Plastic Parts Product

Certifications & Standards

Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
-------------------	---

China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
-----------------------	---

Environmental Disclosure	Product Environmental Profile
--------------------------	---

Circularity Profile	End of Life Information
---------------------	---