


# Product data sheet

Specifications



## PLINTH RAISER W300 H100MM PRISMA G IP30

08807

⚠ Discontinued on: Apr 25, 2023

⚠ Discontinued

### Main

Range	Prisma
Range Of Product	Prisma G
Product Or Component Type	Plinth raiser
Range Compatibility	Prisma Prisma G enclosure
Product Compatibility	IP31 enclosure IP41 enclosure

### Complementary

Installation Description	Floor-standing duct - width 300 mm
Quantity Per Set	Set of 1
Height	100 mm
Width	300 mm
Depth	260 mm
Net Weight	1.44 kg
Surface Finish	Matt Smooth
Protective Treatment	Electrophoresis treatment and hot-polymerised polyester epoxy powder
Colour	White (RAL 9001)

### Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	6.8 cm
Package 1 Width	11.3 cm
Package 1 Length	31 cm
Package 1 Weight	1.72 kg
Unit Type Of Package 2	S04
Number Of Units In Package 2	5
Package 2 Height	30 cm
Package 2 Width	40 cm
Package 2 Length	60 cm

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Package 2 Weight	9.517 kg
Unit Type Of Package 3	P12
Number Of Units In Package 3	40
Package 3 Height	74.5 cm
Package 3 Width	80 cm
Package 3 Length	120 cm
Package 3 Weight	88.136 kg

## Sustainability

**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency   RoHS/REACH

## Well-being performance

✓ Reach Free Of Svhc

✓ Toxic Heavy Metal Free

✓ Mercury Free

✓ Rohs Exemption Information   Yes

✓ Halogen Free Plastic Parts Product

## Certifications & Standards

Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
-------------------	---------------------------------------------------------------------------------------------------

China Rohs Regulation	<a href="#">China RoHS declaration</a> Pro-active China RoHS declaration (out of China RoHS legal scope)
-----------------------	-------------------------------------------------------------------------------------------------------------

Environmental Disclosure	<a href="#">Product Environmental Profile</a>
--------------------------	-----------------------------------------------