

# Product data sheet

Specifications



## Micro Pragma surface enclosure - IP30 - 1x8modules - reversible transparent door

10208

### Main

Range	Micro Pragma
Product Or Component Type	Enclosure
Enclosure Type	Modular enclosure
Nb Of 18 Mm Modules Per Row	8
Nb Of Horizontal Rows	1
Type Of Door	Reversible Transparent
Width	198 mm
Height	200 mm
Depth	72 mm

### Complementary

Enclosure Mounting	Surface
9 Mm Pitches	16
Total Number Of 18 Mm Modules	8
Type Of Rail	DIN
Mounting Plate Description	Without mounting plate
Enclosure Material	Enclosure: self-extinguishing material
Internal Depth	66 mm
Colour	Enclosure: white (RAL 9003)
Market Segment	Small commercial

### Environment

Standards	EN 60439-3 IEC 23-48 IEC 60439-3 IEC 60695-2-1
Fire Resistance	650 °C ( 30 s ) conforming to IEC 60695-2-1
Ip Degree Of Protection	IP40 conforming to IEC 60529 (with installation of devices IP40 minimum)
Ik Degree Of Protection	IK07 conforming to EN 50102

### Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Package 1 Height	7.500 cm
Package 1 Width	20.000 cm
Package 1 Length	20.000 cm
Package 1 Weight	405.000 g
Unit Type Of Package 2	BB1
Number Of Units In Package 2	14
Package 2 Height	23.000 cm
Package 2 Width	40.000 cm
Package 2 Length	59.500 cm
Package 2 Weight	6.220 kg
Unit Type Of Package 3	P12
Number Of Units In Package 3	112
Package 3 Height	60.000 cm
Package 3 Width	80.000 cm
Package 3 Length	120.000 cm
Package 3 Weight	62.000 kg

## Contractual warranty

Warranty	18 months
----------	-----------

# Sustainability




**Green Premium™ label** is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)

## Well-being performance

 Mercury Free	
 Rohs Exemption Information	<a href="#">Yes</a>
 Halogen Free Product	
Reach Regulation	<a href="#">REACH Declaration</a>
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	<a href="#">China RoHS declaration</a> Product out of China RoHS scope. Substance declaration for your information