


Product data sheet

Specifications



pushbutton BP'clic - 1 NC + red pilot light

16189

 **Discontinued on:** Oct 2, 2019

 **Discontinued**

Main

Range Of Product	DuoLine
Range	DuoLine
Product Name	DuoLine BP'clic
Product Or Component Type	Push-button
Device Short Name	BP'clic
Standards	IEC 60669-1 IEC 60947-5-1
Product Certifications	NF

Complementary

Contacts Type And Composition	1 NC
[Ie] Rated Operational Current	20 A
[Ue] Rated Operational Voltage	250 V AC
Control Type	1 push-button grey
Light Source	LED
Cap/Operator Or Lens Colour	Red
Bulb Lifespan	100000 h
Signalling Circuit Voltage	AC: 110...230 V 50/60 Hz
Power Consumption In W	0.3 W
Mounting Mode	Fixed
Mounting Support	35 mm symmetrical DIN rail
Comb Busbar And Distribution Block Compatibility	Upside: Bar'clic Upside: ProDis
9 Mm Pitches	2
Height	82 mm
Width	18 mm
Depth	71.5 mm
Colour	White
Electrical Durability	AC-22: 30000 cycles AC 50/60 Hz
Connections - Terminals	Staggered tunnel terminal2 cable(s) 5 mm² flexible with cable end Staggered tunnel terminal2 cable(s) 5 mm² flexible without cable end Staggered tunnel terminal2 cable(s) 5 mm² rigid with cable end Staggered tunnel terminal2 cable(s) 5 mm² rigid without cable end

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	0.75 cm
Package 1 Width	0.18 cm
Package 1 Length	0.85 cm
Package 1 Weight	0.047 kg

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency RoHS/REACH

Well-being performance

✓ Mercury Free

✓ Rohs Exemption Information [Yes](#)

Certifications & Standards

Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins