

# Product data sheet

Specifications



## Thorsman - nail clip - TC 3 x 5 mm - 1.2/20/15 - bronze - set of 5000

2106720

⚠ Discontinued on: Sep 30, 2022

⚠ Discontinued

### Main

Range	Thorsman
Range Of Product	Thorsman
Product Or Component Type	Nail clip
Device Short Name	TC
Device Application	Installation of flat cable
Product Destination	Flat cable 3 x 5 mm
Type Of Installation	Indoor
Provided Equipment	Nail
Nail Diameter	1.2 mm
Length	20 mm
Embedding Depth	15 mm

### Complementary

Colour Tint	Bronze
Material	Clip: PP (polypropylene) Nail: electroplated hardened steel
Ambient Air Temperature For Operation	-40...80 °C

### Environment

Environmental Characteristic	UV resistant Impact resistant
Quantity Per Set	Set of 5000
Net Weight	0.0003 kg

### Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	0.6 cm
Package 1 Width	0.5 cm
Package 1 Length	0.9 cm
Package 1 Weight	0.3 g
Unit Type Of Package 2	BAG

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Number Of Units In Package 2	25000
Package 2 Height	15.6 cm
Package 2 Width	30.0 cm
Package 2 Length	39.8 cm
Package 2 Weight	7.873 kg

## Contractual warranty

Warranty	18 months
----------	-----------

## Sustainability

**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency   RoHS/REACH

## Well-being performance

✓ Reach Free Of Svhc

✓ Toxic Heavy Metal Free

✓ Mercury Free

✓ Rohs Exemption Information   Yes

## Certifications & Standards

Reach Regulation	<a href="#">REACH Declaration</a>
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
China Rohs Regulation	<a href="#">China RoHS declaration</a> Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	No need of specific recycling operations