

# Product data sheet

Specifications

## Thorsman - TGB 25x2 - fixing band - hole Ø 4 mm - set of 1



2705420

### Main

Range Of Product	Thorsman
Product Or Component Type	Fixing band
Device Short Name	TGB
Quantity Per Set	Set of 1
Type Of Packing	Plastic bag

### Complementary

Material	Cold-rolled steel Galvanised steel
Surface Finish	Zinc coated PELD (polyethylene low density)
Hole Size	Ø 4 mm Ø 8 mm
Practical Load Capacity	7 kN
Width	25 mm
Thickness	2 mm
Length	10 m
Net Weight	2.989 kg

### Environment

Ambient Air Temperature For Operation	-40...100 °C
---------------------------------------	--------------

### Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	4.600 cm
Package 1 Width	23.800 cm
Package 1 Length	25.600 cm
Package 1 Weight	3.132 kg
Unit Type Of Package 2	S02
Number Of Units In Package 2	5
Package 2 Height	15.000 cm
Package 2 Width	30.000 cm

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Package 2 Length	40.000 cm
Package 2 Weight	15.660 kg

## Contractual warranty

Warranty	18 months
----------	-----------

# Sustainability

**Green Premium™ label** is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)



Transparency   RoHS/REACH

## Well-being performance

✓	Reach Free Of Svhc	
✓	Toxic Heavy Metal Free	
✓	Mercury Free	
✓	Rohs Exemption Information	Yes

## Certifications & Standards

Reach Regulation	<a href="#">REACH Declaration</a>
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
China Rohs Regulation	<a href="#">China RoHS declaration</a> Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	No need of specific recycling operations