

# Product data sheet

Specifications



## Thorsman - TSB 4.2x19 - screw - hexagonal - set of 1000

3780716

 **Discontinued on:** Sep 30, 2022

 **Discontinued**

### Main

Range Of Product	Thorsman
Product Or Component Type	Self tapping screw
Device Short Name	TSB
Device Application	Metal sheet 2 x 1.5 mm
Screw Type	Fully threaded with single thread
Tool Type	screwdriver magnetic socket
Quantity Per Set	Set of 1000

### Complementary

Screw Diameter	4.2 mm
Screw Length	19 mm
Shape Of Screw Head	Hexagonal
Screwdriver Shape	Philips No 2
Centring Collar Diameter	8.3 mm
Material	Screw: hardened steel electroplated
Net Weight	0.0018 kg

### Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	0.7 cm
Package 1 Width	0.8 cm
Package 1 Length	2.0 cm
Package 1 Weight	1.8 g
Unit Type Of Package 2	BB1
Number Of Units In Package 2	1000
Package 2 Height	6.0 cm
Package 2 Width	13.2 cm
Package 2 Length	19.4 cm
Package 2 Weight	1.954 kg

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

# Contractual warranty

Warranty	18 months
----------	-----------

## Sustainability

**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency   RoHS/REACH

## Well-being performance

✓ Reach Free Of Svhc

✓ Toxic Heavy Metal Free

✓ Mercury Free

✓ Rohs Exemption Information   Yes

## Certifications & Standards

Reach Regulation	<a href="#">REACH Declaration</a>
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
China Rohs Regulation	<a href="#">China RoHS declaration</a> Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	No need of specific recycling operations