

# Product data sheet

Specifications



## Polinorma - cable tray - perforated - 60x100 mm - grey

43111110

 **Discontinued on:** Jun 30, 2023

 **Discontinued**

### Main

|                           |                 |
|---------------------------|-----------------|
| Range Of Product          | Polinorma       |
| Product Or Component Type | Cable tray      |
| Cable Tray Type           | Perforated      |
| Colour                    | Grey (RAL 7030) |
| Quantity Per Set          | 12 m            |

### Complementary

|           |                          |
|-----------|--------------------------|
| Material  | PVC (polyvinyl chloride) |
| Height    | 60 mm                    |
| Width     | 100 mm                   |
| Length    | 3 m                      |
| Thickness | 2.2 mm                   |

### Environment

|                                       |  |
|---------------------------------------|--|
| Flame Retardance                      | V0                                       |
| Standards                             | IEC 61537<br>UNE 23727<br>EN 60695-11-10 |
| Ambient Air Temperature For Operation | -20...60 °C                              |
| Ip Degree Of Protection               | IP2X                                     |
| Ik Degree Of Protection               | IK10                                     |

### Packing Units

|                              |          |
|------------------------------|----------|
| Unit Type Of Package 1       | PCE      |
| Number Of Units In Package 1 | 1        |
| Package 1 Height             | 12.0 cm  |
| Package 1 Width              | 12.0 cm  |
| Package 1 Length             | 300.0 cm |
| Package 1 Weight             | 875.0 g  |
| Unit Type Of Package 2       | BB1      |
| Number Of Units In Package 2 | 12       |
| Package 2 Height             | 12.0 cm  |

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

|                              |           |
|------------------------------|-----------|
| Package 2 Width              | 12.0 cm   |
| Package 2 Length             | 300.0 cm  |
| Package 2 Weight             | 10.505 kg |
| Unit Type Of Package 3       | PAL       |
| Number Of Units In Package 3 | 432       |
| Package 3 Height             | 65.0 cm   |
| Package 3 Width              | 300.0 cm  |
| Package 3 Length             | 120.0 cm  |
| Package 3 Weight             | 398.18 kg |

## Sustainability

**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency   RoHS/REACH

## Well-being performance

✓ Reach Free Of Svhc

✓ Toxic Heavy Metal Free

✓ Mercury Free

✓ Rohs Exemption Information   Yes

## Certifications & Standards

|                          |   |
|--------------------------|---|
| Reach Regulation         | <a href="#">REACH Declaration</a>   |
| Eu Rohs Directive        | Pro-active compliance (Product out of EU RoHS legal scope)<br><a href="#">EU RoHS Declaration</a>           |
| China Rohs Regulation    | <a href="#">China RoHS declaration</a><br>Pro-active China RoHS declaration (out of China RoHS legal scope) |
| Environmental Disclosure | <a href="#">Product Environmental Profile</a>   |
| Circularity Profile      | No need of specific recycling operations  |