


Product data sheet

Specifications



Performa - mesh tray - electro-zinc - 70 mm x 400 mm x 3000 mm

4511240

 **Discontinued on:** Jan 3, 2022

 **Discontinued**

Important message: This product belongs to Cable Support which is no longer commercialized by Schneider Electric. As per the first of January 2022 the commercialization is managed by Wibe-Group, Please follow the link www.wibe-group.com for further details.

Main

Range Of Product	Performa
Product Or Component Type	Mesh tray
Quantity Per Set	6 m

Complementary

Shape	U-shape
Material	Steel (electro-zinc)
Atmospheric-Corrosivity Category	C1
Longitudinal Wire Diameter	4.9 mm
Transversal Wire Diameter	3.9 mm
Cable Cross Section	25728 mm²
Standards	EN 12329 EN 50102 IEC 60068-2-75 DIN 4102-12 IEC 61537 EN/ISO 9227
Length	3 m
Height	75 mm
Width	400 mm
Height Compatibility	70 mm
Width Compatibility	400 mm
Surface Treatment Compatibility	Electro-zinc

Environment

Ambient Air Temperature For Operation	-40...120 °C
Ik Degree Of Protection	IK10

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	9 cm

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Package 1 Width	41 cm
Package 1 Length	300 cm
Package 1 Weight	3 kg

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency RoHS/REACH

Well-being performance

✓ Reach Free Of Svhc

✓ Toxic Heavy Metal Free

✓ Mercury Free

✓ Rohs Exemption Information Yes

Certifications & Standards

Reach Regulation	REACH Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations