

Product data sheet

Specifications



Thorsman - INKA-TSU161-2 - T-piece rising/front cover - 72 mm - natural

5510240

 **Discontinued on:** Jun 30, 2022

 **Discontinued**

Main

| | |
|---------------------------|--------------------|
| Range Of Product | Thorsman |
| Product Name | Thorsman INKA |
| Product Or Component Type | T-piece |
| Trunking Dimension | 161 x 72 mm |
| Trunking Material | Aluminium |
| Direction Change Type | Upward |
| Device Composition | Front cover |
| Colour Tint | Natural |
| Material | Aluminium anodized |
| Quantity Per Set | Set of 1 |
| Market Segment | Small commercial |

Complementary

| | |
|--------|--------|
| Length | 360 mm |
| Height | 260 mm |
| Width | 72 mm |

Environment

| | |
|---------------------------------------|--------------------------------------|
| Directives | 2014/35/EU - low voltage directive |
| Standards | EN 50085-1 73/23/EEC 93/68/EEC |
| Ambient Air Temperature For Operation | -20...60 °C |
| Ip Degree Of Protection | IP20 |

Packing Units

| | |
|------------------------------|---------|
| Unit Type Of Package 1 | PCE |
| Number Of Units In Package 1 | 1 |
| Package 1 Height | 7 cm |
| Package 1 Width | 26 cm |
| Package 1 Length | 36 cm |
| Package 1 Weight | 1.16 kg |

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Contractual warranty

| | |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency RoHS/REACH

Well-being performance

✓ Reach Free Of Svhc

✓ Toxic Heavy Metal Free

✓ Mercury Free

✓ Rohs Exemption Information Yes

Certifications & Standards

| | |
|--------------------------|---|
| Reach Regulation | REACH Declaration |
| Eu Rohs Directive | Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration |
| China Rohs Regulation | China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope) |
| Environmental Disclosure | Product Environmental Profile |
| Circularity Profile | No need of specific recycling operations |