


# Product data sheet

Specifications



## Wibe - tightening loop HT-621 - steel hot-dip galvanized

713690

 **Discontinued on:** Jan 3, 2022

 **Discontinued**

**Important message:** This product belongs to Cable Support which is no longer commercialized by Schneider Electric. As per the first of January 2022 the commercialization is managed by Wibe-Group, Please follow the link [www.wibe-group.com](http://www.wibe-group.com) for further details.

### Main

|                           |  |
|---------------------------|--|
| Range                     | Wibe   |
| Range Of Product          | Wibe Cable Ladders   |
| Product Or Component Type | Tightening loop  |
| Device Short Name         | HT-621   |
| Mounting Location         | Area with high level of environmental corrosion, humidity and airborne pollution industrial and coastal areas, chemical plants |

### Complementary

|                                 |   |
|---------------------------------|---|
| Mounting Support                | HT-11 end bracket<br>5L angle bracket<br>HT-14 wall bracket |
| Material With Surface Treatment | Steel, hot-dip galvanized                                   |
| Corrosion Class                 | C3/C4   |
| Height                          | 50 mm   |
| Width                           | 270 mm  |
| Depth                           | 50 mm   |
| Net Weight                      | 18 kg / set of 100  |

### Packing Units

|                              |         |
|------------------------------|---------|
| Unit Type Of Package 1       | PCE     |
| Number Of Units In Package 1 | 1       |
| Package 1 Height             | 1.3 cm  |
| Package 1 Width              | 2.1 cm  |
| Package 1 Length             | 28.1 cm |
| Package 1 Weight             | 180 g   |

### Contractual warranty

|          |           |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

## Sustainability

**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency   RoHS/REACH

## Well-being performance

|   |                            |     |
|---|----------------------------|-----|
| ✓ | Reach Free Of Svhc         |     |
| ✓ | Toxic Heavy Metal Free     |     |
| ✓ | Mercury Free               |     |
| ✓ | Rohs Exemption Information | Yes |

## Certifications & Standards

|                          |   |
|--------------------------|---|
| Reach Regulation         | <a href="#">REACH Declaration</a>   |
| Eu Rohs Directive        | Pro-active compliance (Product out of EU RoHS legal scope)<br><a href="#">EU RoHS Declaration</a>           |
| China Rohs Regulation    | <a href="#">China RoHS declaration</a><br>Pro-active China RoHS declaration (out of China RoHS legal scope) |
| Environmental Disclosure | <a href="#">Product Environmental Profile</a>   |
| Circularity Profile      | No need of specific recycling operations  |