

# Product data sheet

Specifications



## Motion Sensor 752 series - Passive infrared - Indoor - Two-channel - 15m detection radius - 240 V

752IR2RC

 To be discontinued on: Apr 30, 2024

 To be discontinued

### Main

Range Of Product	ARGUS standard movement detector
Range	ARGUS
Product Or Component Type	Presence detector with IR receiver
Load Type	LED lighting: : 100 W Incandescent lamps: : 2000 W - 230 V Halogen lamp: : 1000 W - 230 V Fluorescent tube: 900 VA Compact fluorescent lamp: : 100 W Motor: : 100 W Relay: : 5 A - 250 V
Colour Tint	White

### Complementary

Network Frequency	50/60 Hz
Input Function	Switch External trigger
Output Voltage	220...250 V
Number Output Current	10 A
Number Of Channels	2
Control Type	Movement sensor
Function Available	Switching, toggling, dimming
Light Intensity Adjustment	10...2000 lux
Horizontal Detection Angle	360 °
Detection Range	Radius: 14000 mm
Device Mounting	Surface Flush
Mounting Height	2.5 m

### Environment

Ip Degree Of Protection	IP52 IP40
-------------------------	--------------

### Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Package 1 Height	13.6 cm
Package 1 Width	12.1 cm
Package 1 Length	17.8 cm
Package 1 Weight	433.1 g

## Sustainability

**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency   RoHS/REACH

## Well-being performance

✓ Reach Free Of Svhc

✓ Rohs Exemption Information   [Yes](#)

## Certifications & Standards

Reach Regulation	<a href="#">REACH Declaration</a>
Eu Rohs Directive	Compliant <a href="#">EU RoHS Declaration</a>
China Rohs Regulation	<a href="#">China RoHS declaration</a> Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins