

Product data sheet

Specifications



Illuminated push-button head,
Harmony 9001SK, plastic,
mushroom 41mm, red, 30mm, 2
positions, push-pull, 24-28V

9001SKR9P35R

Main

| | |
|---------------------------------|----------------------------------|
| Range Of Product | Harmony 9001SK |
| Product Or Component Type | Head for illuminated push-button |
| Device Short Name | 9001SK |
| Operator Additional Information | Screw-on plastic |

Complementary

| | |
|-------------------------------|-----------------------|
| Bezel Material | Plastic |
| Mounting Diameter | 30 mm |
| Contacts Type And Composition | Without contact block |
| Mechanical Durability | 5000000 cycles |
| Device Presentation | Basic element |
| Cap/Operator Or Lens Colour | Red |
| [Us] Rated Supply Voltage | 24...28 V |
| Light Block Supply | Full voltage |
| Operator Profile | Mushroom Ø 41 mm |
| Type Of Operator | Push-pull |
| Operator Position Information | 2 positions |
| Size | 30 mm |
| Bulb Base | BA 9s |
| Light Source | Incandescent bulb |

Environment

| | |
|---------------------------|--|
| Standards | UL 508 JIS C 852 JIS C 4520 EN/IEC 60947-5-1 EN/IEC 60947-1 CSA C22.2 No 14 EN/IEC 60947-5-4 |
| Ip Degree Of Protection | IP66 |
| Nema Degree Of Protection | NEMA 1/2/3/3R/4/4X/6/12/13 |

Packing Units

| | |
|------------------------------|-----|
| Unit Type Of Package 1 | PCE |
| Number Of Units In Package 1 | 1 |

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

| | |
|------------------|-----------|
| Package 1 Height | 12.903 cm |
| Package 1 Width | 5.08 cm |
| Package 1 Length | 32.774 cm |
| Package 1 Weight | 99.79 g |

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency RoHS/REACH

Well-being performance

✓ Reach Free Of Svhc

✓ Toxic Heavy Metal Free

✓ Mercury Free

✓ Rohs Exemption Information [Yes](#)

Certifications & Standards

| | |
|---------------------------|---|
| Reach Regulation | REACH Declaration |
| Eu Rohs Directive | Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration |
| China Rohs Regulation | China RoHS declaration |
| Environmental Disclosure | Product Environmental Profile |
| Weee | The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins |
| Circularity Profile | No need of specific recycling operations |
| California Proposition 65 | WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov |