

# Product data sheet

Specifications



## SELECTOR SWITCH 600VAC 10A 30MM T-K

9001KS11K1H5SR251

 **Discontinued on:** Jan 29, 2021

 **Discontinued**

### Main

|                           |                         |
|---------------------------|-------------------------|
| Range Of Product          | Harmony 9001K           |
| Product Or Component Type | Selector switch         |
| Device Short Name         | K                       |
| Type Of Operator          | maintained              |
| Operator Profile          | Black key operated knob |

### Complementary

|                               |   |
|-------------------------------|---|
| Bezel Material                | Chromium plated metal   |
| Mounting Diameter             | 30 mm   |
| Operator Position Information | 2 positions   |
| Connections - Terminals       | Screw-clamp terminals, 1 x 0.22...2 x 1.5 mm <sup>2</sup> conforming to IEC 60947-1 |
| Device Presentation           | Complete product  |

### Environment

|                           |   |
|---------------------------|---|
| Nema Degree Of Protection | NEMA 1/2/3/3R/4/6/12/13   |
| Product Certifications    | CE<br>CSA LR24590 class 3211 03<br>UL listed file E42259 CCN NKCR |

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

## Sustainability

**Green Premium™** label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency   RoHS/REACH

## Well-being performance



Mercury Free



RoHS Exemption Information

Yes

## Certifications & Standards

|                           |  |
|---------------------------|--|
| Reach Regulation          | <a href="#">REACH Declaration</a>  |
| Eu Rohs Directive         | Pro-active compliance (Product out of EU RoHS legal scope)   |
| China Rohs Regulation     | <a href="#">China RoHS declaration</a>   |
| Environmental Disclosure  | <a href="#">Product Environmental Profile</a>  |
| Weee                      | The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins  |
| Circularity Profile       | No need of specific recycling operations   |
| California Proposition 65 | WARNING: This product can expose you to chemicals including: Nickel compounds, which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a> |