


Product data sheet

Specifications



CONTROL STATION + OPERATORS

9001KYSK105

 **Discontinued on:** Jul 1, 2020

 **Discontinued**

Main

Range Of Product	Harmony 9001KY
Product Or Component Type	Control station
Device Short Name	9001KY
Provided Equipment	Label plate with STOP marking
Contact Block Name	KA3
Product Specific Application	For hoisting and mechanical handling applications
Level Or Class	Class III Class II Division 2 Group G

Complementary

Enclosure/Cubicle Description	Wall-mounted enclosure with 1 cut-out: Ø 30 mm
Enclosure Material	Stainless steel
Type Of Installation	Indoor/outdoor
Control Station Composition	1 push-button with 1 NC contacts
Mechanical Interlocking	Without mechanical interlock
Connector Type	Screw clamp connector
Connections - Terminals	Direct connection (AWG 2) solid stranded Direct connection (AWG 12) solid stranded Direct connection (AWG 24) solid stranded
[Ue] Rated Operational Voltage	300 V
[Ie] Rated Operational Current Ac	10 A

Environment

Nema Degree Of Protection	NEMA 13 NEMA 4 NEMA 3 NEMA 1
Environmental Characteristic	Resistant against immersion in water Dust and oil resistant
Product Certifications	UL listed
Ambient Air Temperature For Operation	-25...60 °C
Ambient Air Temperature For Storage	-40...70 °C

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency RoHS/REACH

Well-being performance

✓	Reach Free Of Svhc	
✓	Toxic Heavy Metal Free	
✓	Mercury Free	
✓	Rohs Exemption Information	Yes

Certifications & Standards

Reach Regulation	REACH Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations
California Proposition 65	WARNING: This product can expose you to chemicals including: Nickel compounds, which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov