

# Product data sheet

Specifications



Selector switch, Harmony 9001SK,  
plastic, standard handle, black,  
30mm, 3 positions, stay put, 2 C/O

9001SKS44BH2

## Main

Range Of Product	Harmony 9001SK
Product Or Component Type	Selector switch
Device Short Name	9001SK

## Complementary

Bezel Material	Plastic
Mounting Diameter	30 mm
Operator Position Information	3 positions
Contacts Type And Composition	2 C/O
Device Presentation	Complete product
Cap/Operator Or Lens Colour	Black
Operator Profile	Standard handle
Type Of Operator	Stay put
Size	30 mm
Cam Profile	4

## Environment

Protective Treatment	TC
Ambient Air Temperature For Storage	-40...70 °C
Ambient Air Temperature For Operation	-25...70 °C
Electrical Shock Protection Class	Class II conforming to IEC 61140
Ip Degree Of Protection	IP66 conforming to IEC 60529
Nema Degree Of Protection	NEMA 1/2/3/3R/4/4X/6/12/13
Product Certifications	CE UL listed file E42259 CCN NKCR CSA LR24590 class 3211 03

## Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	12.903 cm
Package 1 Width	5.08 cm
Package 1 Length	32.774 cm

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

---

Package 1 Weight	90.719 g
------------------	----------

## Sustainability

**Green Premium™** label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency   RoHS/REACH

## Well-being performance

✓ Reach Free Of Svhc

✓ Toxic Heavy Metal Free

✓ Mercury Free

✓ Rohs Exemption Information   Yes

## Certifications & Standards

Reach Regulation	<a href="#">REACH Declaration</a>
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
China Rohs Regulation	<a href="#">China RoHS declaration</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	No need of specific recycling operations
California Proposition 65	WARNING: This product can expose you to chemicals including: Nickel compounds, which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a>