

# Product data sheet

Specifications



## Modbus Plus drop cable - between Momentum I/O sub-base and T-junction - 6 m

990NAD21130

### Main

Accessory / Separate Part Category	Connection accessories
Accessory / Separate Part Type	Drop connection cable
Accessory / Separate Part Designation	Modbus Plus drop cable
Accessory / Separate Part Destination	Modbus Plus network

### Complementary

Product Compatibility	990NAD23020 990NAD23000 490NRP25300 990NAD23010 990NAD23021 NWPB85002 STBNMP2212 140CPU43412U 140CPU31110
Range Compatibility	Modicon Momentum automation platform Modicon Premium automation platform Advantys STB distributed I/O solutions Lexium 15 Modicon Quantum automation platform
Cable Length	6 m
Electrical Connection	1 male connector SUB-D 9 elbowed communication module side Free end local site tap side
Net Weight	0.53 kg

### Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	2.500 cm
Package 1 Width	20.900 cm
Package 1 Length	24.800 cm
Package 1 Weight	362.000 g
Unit Type Of Package 2	S03
Number Of Units In Package 2	25
Package 2 Height	30.000 cm
Package 2 Width	30.000 cm
Package 2 Length	40.000 cm

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Package 2 Weight	9.619 kg
------------------	----------

## Contractual warranty

Warranty	18 months
----------	-----------

## Sustainability

**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency

## Well-being performance

✓ Toxic Heavy Metal Free

✓ Mercury Free

✓ Rohs Exemption Information [Yes](#)

<b>Eu Rohs Directive</b>	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
--------------------------	---

<b>China Rohs Regulation</b>	<a href="#">China RoHS declaration</a>
------------------------------	--

<b>Environmental Disclosure</b>	<a href="#">Product Environmental Profile</a>
---------------------------------	---

<b>Circularity Profile</b>	No need of specific recycling operations
----------------------------	--

<b>California Proposition 65</b>	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a>
----------------------------------	---