

Product data sheet

Specifications



Acti9 IC60 RCBO - auxiliary contact - 1OF/SD - AC/DC

A9A19803

Main

Range Of Product	Acti9
Product Or Component Type	OC or fault contact
Device Short Name	iOF/SD
Signal Contacts Composition	1 C/O
[In] Rated Current	6 A at 24 V, DC 2 A at 60 V, DC 1.5 A at 110 V, DC 1 A at 250 V, DC 6 A at 24...230 V, AC 50 Hz 3 A at 415 V, AC 50 Hz
9 Mm Pitches	1

Complementary

Mounting Mode	Clip-on
Mounting Support	DIN rail
Height	86 mm
Width	9 mm
Depth	71 mm
Net Weight	36 g
Colour	White
Connections - Terminals	Screw clamp terminal (bottom) 1 cable(s) 0.25...4 mm ² - rigid Screw clamp terminal (bottom) 1 cable(s) 0.25...2.5 mm ² - flexible Screw clamp terminal (bottom) 2 cable(s) 1.5 mm ² - rigid Screw clamp terminal (bottom) 2 cable(s) 1.5 mm ² - flexible Screw clamp terminal (bottom) 1 cable(s) 2.5 mm ² - flexible with ferrule
Wire Stripping Length	6 mm for bottom connection
Tightening Torque	0.6 N.m bottom

Environment

Standards	EN/IEC 60947-5-1
Ambient Air Temperature For Operation	-25...60 °C
Ambient Air Temperature For Storage	-40...70 °C

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Package 1 Height	2.5 cm
Package 1 Width	8.5 cm
Package 1 Length	10.4 cm
Package 1 Weight	52 g
Unit Type Of Package 2	S03
Number Of Units In Package 2	72
Package 2 Height	30 cm
Package 2 Width	30 cm
Package 2 Length	40 cm
Package 2 Weight	4.286 kg

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.


[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency RoHS/REACH

Well-being performance

 Rohs Exemption Information [Yes](#)

Certifications & Standards

Reach Regulation	REACH Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	End of Life Information