

Product data sheet

Specifications



ARGUS Presence HF High Bay - 2ch

CCT551023

Main

Range Of Product	ARGUS standard movement detector
Range	ARGUS
Product Or Component Type	Presence detector
Load Type	LED lighting: : 100 W Incandescent lamps: : 2000 W - 230 V Halogen lamp: : 1000 W - 230 V Fluorescent tube: 900 VA Compact fluorescent lamp: : 100 W Motor: : 100 W Relay: : 5 A - 250 V Halogen lamp with standard electronic transformer: 1000 VA Halogen lamp with standard ferromagnetic transformer: 1000 VA
Colour Tint	White

Complementary

Network Frequency	50/60 Hz
Input Function	Switch
Output Voltage	220...250 V
Number Output Current	10 A
Number Of Channels	2
Control Type	Movement sensor
Function Available	Switching, toggling, dimming
Light Intensity Adjustment	10...2000 lux
Horizontal Detection Angle	360 °
Detection Range	Radius: 7000 mm
Technology Type	High frequency
Mounting Height	2.5 m

Environment

Ip Degree Of Protection	IP40 IP52
-------------------------	--------------

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	12.2 cm

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Package 1 Width	13 cm
Package 1 Length	16.2 cm
Package 1 Weight	498 g
Unit Type Of Package 2	S03
Number Of Units In Package 2	6
Package 2 Height	30 cm
Package 2 Width	30 cm
Package 2 Length	40 cm
Package 2 Weight	3.492 kg
Unit Type Of Package 3	P12
Number Of Units In Package 3	144
Package 3 Height	104 cm
Package 3 Width	80 cm
Package 3 Length	120 cm
Package 3 Weight	97 kg

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency RoHS/REACH

Well-being performance

 Rohs Exemption Information [Yes](#)

Certifications & Standards

Reach Regulation	REACH Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	End of Life Information