

# Product data sheet

Specifications



## Odace/Unica Wireless - keyring remote control - 4 channels - dark grey

CCT1A010

⚠ Discontinued on: Dec 15, 2021

⚠ Discontinued

### Main

Range Of Product	Unica Wireless Odace
Range Compatibility	Unica Wireless Odace Wireless Free RF IHC Alvais RF
Product Or Component Type	Keyring remote control
Transmission Frequency	868.3 MHz
Provided Equipment	Lithium battery
Colour Tint	Dark grey

### Complementary

Operating Distance	10...50 m indoor <= 300 m outdoor
Number Of Channels	4
Number Of Batteries	1 CR2032 lithium battery 3 V - autonomy: 5...7 years
Standards	EN 61001-6-3 EN 61000-6-2 IEC 60068-2-27 IEC 60068-2-6 99/5/EEC ETSI EN 300 220-1 ETSI EN 300 220-2 2004/108/EC
Ambient Air Temperature For Operation	-5...50 °C
Relative Humidity	20...95 %
Height	57 mm
Width	44 mm
Depth	12 mm

### Environment

Ip Degree Of Protection	IP20
-------------------------	------

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Environmental Characteristic	UV resistant Oil Bleach Liquid soap Acetone Petrol Window-cleaning fluid Alcohol
------------------------------	---

## Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	6.3 cm
Package 1 Width	9.7 cm
Package 1 Length	10.7 cm
Package 1 Weight	96 g

## Contractual warranty

Warranty	18 months
----------	-----------

## Sustainability

**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency   RoHS/REACH

## Well-being performance

✓ Mercury Free

✓ Rohs Exemption Information   [Yes](#)

## Certifications & Standards

Reach Regulation	<a href="#">REACH Declaration</a>
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	<a href="#">China RoHS declaration</a> Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	<a href="#">End of Life Information</a>