


Product data sheet

Specifications



Odace/Unica Wireless - universal receiver relay - 230 VAC - fuse protection,grey

CCT1A031

⚠ Discontinued on: Jan 31, 2024

⚠ Discontinued

Main

Range Compatibility	Odace Wireless Free RF IHC Unica Wireless Alvais RF
Product Or Component Type	Universal receiver relay
Transmission Frequency	868.3 MHz
[Ue] Rated Operational Voltage	127/230 V AC +/- 10 % at 50/60 Hz
Colour Tint	Grey

Complementary

Wiring Device Mounting	Flush
Operating Distance	10...50 m indoor <= 100 m outdoor
Load Type	230 V AC halogen lamp: 5...2000 W 230 V AC incandescent lamp: 5...2300 W Low voltage halogen lamp with electronic transformer: 5...500 VA Low voltage halogen lamp with ferromagnetic transformer: 5...500 VA Low voltage halogen lamp with toroidal transformer: 5...500 VA Motor: 5...690 VA Fan: 5...690 VA Compact fluorescent lamp: 5...880 VA LED lamp: 5...880 VA Fluorescent tube: 5...920 VA
Load Interrupting Current	Light: 10 A Motor: 3 A
Protection Type	Fuse protection
Standards	EN 61000-6-2 ETSI EN 301 489 EN 61000-6-3 89/336/EEC EN 60669-1 99/5/EEC EN 60669-2-1 ETSI EN 300 220
Ambient Air Temperature For Operation	-5...50 °C
Relative Humidity	20...95 %
Height	46 mm
Width	46 mm
Depth	23 mm
Cable Length	0.2 m

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Environment

Ip Degree Of Protection	IP20
-------------------------	------

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	6.3 cm
Package 1 Width	10.0 cm
Package 1 Length	10.7 cm
Package 1 Weight	128.0 g
Unit Type Of Package 2	S03
Number Of Units In Package 2	34
Package 2 Height	30.0 cm
Package 2 Width	30.0 cm
Package 2 Length	40.0 cm
Package 2 Weight	4.743 kg

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability

Green Premium™ label is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)



Transparency RoHS/REACH

Well-being performance

✓ Mercury Free

✓ Rohs Exemption Information [Yes](#)

Certifications & Standards

Reach Regulation	REACH Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	End of Life Information