

Product data sheet

Specifications



Stago - t-piece 60x300mm 1mm hot-dip galvanized

CSU361530124

 **Discontinued on:** Jan 3, 2022

 **Discontinued**

Important message: This product belongs to Cable Support which is no longer commercialized by Schneider Electric. As per the first of January 2022 the commercialization is managed by Wibe-Group, Please follow the link www.wibe-group.com for further details.

Main

| | |
|---------------------------|---------|
| Product Or Component Type | T-piece |
|---------------------------|---------|

Complementary

| | |
|-----------------------|-------------------------------------|
| Operating Angle | 90 ° |
| Direction Change Type | Horizontal |
| Adjustment | Fixed |
| Product Destination | Cable tray TV184 H= 60 mm W= 300 mm |
| Fixing Mode | Screwless |
| Material | Steel hot-dip galvanized |
| Inner Radius | 100 mm |
| Height | 60 mm |
| Width | 540 mm |
| Depth | 420 mm |

Environment

| | |
|----------------------------------|--|
| Atmospheric-Corrosivity Category | C3/C4 |
| Environmental Characteristic | Area with high level of environmental corrosion, humidity and airborne pollution industrial and coastal areas, chemical plants |

Packing Units

| | |
|------------------------------|----------|
| Unit Type Of Package 1 | PCE |
| Number Of Units In Package 1 | 1 |
| Package 1 Height | 6 cm |
| Package 1 Width | 56 cm |
| Package 1 Length | 68 cm |
| Package 1 Weight | 2.365 kg |

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency RoHS/REACH

Well-being performance

| | | |
|---|----------------------------|-----|
| ✓ | Reach Free Of Svhc | |
| ✓ | Toxic Heavy Metal Free | |
| ✓ | Mercury Free | |
| ✓ | Rohs Exemption Information | Yes |

Certifications & Standards

| | |
|--------------------------|---|
| Reach Regulation | REACH Declaration |
| Eu Rohs Directive | Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration |
| China Rohs Regulation | China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope) |
| Environmental Disclosure | Product Environmental Profile |
| Circularity Profile | No need of specific recycling operations |