

# Product data sheet

Specifications



## Performa - fast-fix suspended bracket - ZnAlMg - 20 mm x 300 mm x 40 mm

CSU4538520

⚠ Discontinued on: Jan 3, 2022

⚠ Discontinued

Important message: This product belongs to Cable Support which is no longer commercialized by Schneider Electric. As per the first of January 2022 the commercialization is managed by Wibe-Group, Please follow the link [www.wibe-group.com](http://www.wibe-group.com) for further details.

### Main

|                           |                            |
|---------------------------|----------------------------|
| Product Or Component Type | Fast-fix suspended bracket |
| Quantity Per Set          | Set of 6                   |

### Complementary

|                                  |                          |
|----------------------------------|--------------------------|
| Permanent Permissible Load       | 138 kg                   |
| Product Destination              | Mesh tray zinc+          |
| Mounting Support                 | Threaded rod             |
| Material                         | Steel (zinc+)            |
| Atmospheric-Corrosivity Category | C3/C4                    |
| Height                           | 20 mm                    |
| Width                            | 40 mm                    |
| Depth                            | 300 mm                   |
| Height Compatibility             | 70 mm<br>105 mm<br>35 mm |
| Width Compatibility              | 200 mm                   |
| Surface Treatment Compatibility  | Zinc+                    |

### Packing Units

|                              |       |
|------------------------------|-------|
| Unit Type Of Package 1       | PCE   |
| Number Of Units In Package 1 | 1     |
| Package 1 Height             | 2 cm  |
| Package 1 Width              | 4 cm  |
| Package 1 Length             | 30 cm |
| Package 1 Weight             | 225 g |

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

## Sustainability

**Green Premium™ label** is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)



Transparency   RoHS/REACH

## Well-being performance

✓ Reach Free Of Svhc

✓ Toxic Heavy Metal Free

✓ Mercury Free

✓ Rohs Exemption Information   Yes

## Certifications & Standards

|                          |   |
|--------------------------|---|
| Reach Regulation         | <a href="#">REACH Declaration</a>   |
| Eu Rohs Directive        | Pro-active compliance (Product out of EU RoHS legal scope)<br><a href="#">EU RoHS Declaration</a>           |
| China Rohs Regulation    | <a href="#">China RoHS declaration</a><br>Pro-active China RoHS declaration (out of China RoHS legal scope) |
| Environmental Disclosure | <a href="#">Product Environmental Profile</a>   |
| Circularity Profile      | No need of specific recycling operations  |