

# Product data sheet

Specifications



## Stago - cover external rising piece 300mm stainless steel AISI 304

CSU70653030

 **Discontinued on:** Jan 3, 2022

 **Discontinued**

**Important message:** This product belongs to Cable Support which is no longer commercialized by Schneider Electric. As per the first of January 2022 the commercialization is managed by Wibe-Group, Please follow the link [www.wibe-group.com](http://www.wibe-group.com) for further details.

### Main

Range	Stago
Product Or Component Type	Cover
Mounting Location	Area with almost permanent high levels of humidity and airborne pollution tunnels and dockyards

### Complementary

Operating Angle	90 °
Direction Change Type	Vertical
Product Destination	Rising piece ES114 for cable tray 60 mm 300 mm width Rising piece ES114 for cable tray 110 mm 300 mm width
Fixing Mode	Screwless
Material With Surface Treatment	Stainless steel AISI 304
Corrosion Class	C5-I
Length	299 mm
Height	299 mm
Width	305 mm
Net Weight	1.35 kg / set of 1

### Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	30.1 cm
Package 1 Width	30.1 cm
Package 1 Length	30.5 cm
Package 1 Weight	1.5 kg

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

## Sustainability

**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency   RoHS/REACH

## Well-being performance

✓ Reach Free Of Svhc

✓ Toxic Heavy Metal Free

✓ Mercury Free

✓ Rohs Exemption Information   Yes

## Certifications & Standards

Reach Regulation	<a href="#">REACH Declaration</a>
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
China Rohs Regulation	<a href="#">China RoHS declaration</a> Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	No need of specific recycling operations