

# Product data sheet

Specifications



## Stago - internal / external riser adjustable H51100 100x400mm pre-galvanized

CSU737958

 **Discontinued on:** Jan 3, 2022

 **Discontinued**

**Important message:** This product belongs to Cable Support which is no longer commercialized by Schneider Electric. As per the first of January 2022 the commercialization is managed by Wibe-Group, Please follow the link [www.wibe-group.com](http://www.wibe-group.com) for further details.

### Main

|                           |   |
|---------------------------|---|
| Range Of Product          | Stago   |
| Product Or Component Type | Riser   |
| Cable Support Type        | High side   |
| Mounting Location         | Partly outdoor environment with low exposure to corrosion ware-houses and parking garages |

### Complementary

|                                 |   |
|---------------------------------|---|
| Product Destination             | Cable ladder LB4000 H= 100 mm W= 400 mm |
| Type Of Rung                    | C-profile                               |
| Fixation Rung                   | Welded                                  |
| Fixing Mode                     | By screw                                |
| Material With Surface Treatment | Steel pre-galvanized                    |
| Corrosion Class                 | C2                                      |
| Perforation Location            | Side perforation                        |
| Height                          | 100 mm                                  |
| Width                           | 400 mm                                  |
| Depth                           | 894 mm                                  |
| Net Weight                      | 4.618 kg / set of 1                     |

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

## Sustainability

**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency   RoHS/REACH

## Well-being performance

✓ Reach Free Of Svhc

✓ Toxic Heavy Metal Free

✓ Mercury Free

✓ Rohs Exemption Information   Yes

## Certifications & Standards

|                          |   |
|--------------------------|---|
| Reach Regulation         | <a href="#">REACH Declaration</a>   |
| Eu Rohs Directive        | Pro-active compliance (Product out of EU RoHS legal scope)<br><a href="#">EU RoHS Declaration</a>           |
| China Rohs Regulation    | <a href="#">China RoHS declaration</a><br>Pro-active China RoHS declaration (out of China RoHS legal scope) |
| Environmental Disclosure | <a href="#">Product Environmental Profile</a>   |
| Circularity Profile      | No need of specific recycling operations  |